Brother BWS-1D450-110 printer ribbon Black



Brand : Brother

Product code: BWS-1D450-110

Product name : BWS-1D450-110

- High capacity at 450 metres length per ribbon
- 110mm in width
- High quality thermal transfer ink ribbon
- Ensure clear, durable results
- Standard wax with black ink
- Requires compatible label roll

The BWS-1D450-110 standard wax thermal transfer black ink ribbon, 450 metres in length and 110mm in width has been Certified by Brother International Europe.



Brother BWS-1D450-110 printer ribbon Black:

This high capacity standard wax ribbon has been developed to meet your professional label printing needs. For use in transport and logistics and manufacturing, you can use these 110mm wide ribbons for barcode printing and a variety of other applications. Wax thermal transfer ribbons are cost-effective and best suited to standard paper labels. The BWS-1D450-110 wax ribbons are used in conjunction with compatible label rolls in your industrial label printer.

Performance	
Printing colours	Black
Print technology	Inkjet
Product colour	Black
Country of origin	Spain
Brand compatibility	Brother
Compatibility *	TJ-4020TN, TJ-4120TN, TJ-4021TN, TJ-4121TN
Technical details	
Master (outer) cases per pallet layer	13 pc(s)
Layers per pallet	8 pc(s)
Pallet type	800 x 1200 mm
Weight & dimensions	
Width	70 mm
Depth	70 mm

Weight & dimensions	
Height	110 mm
Weight	470 g
Ribbon width	11 cm
Ribbon length	450 m
Packaging data	
Package weight	4.18 kg
Quantity per pack	1 pc(s)
Logistics data	
Products per pallet	832 pc(s)
Pallet gross weight	456.9 kg
Pallet gross height	11.5 cm
Master (outer) cases per pallet	104 pc(s)
Harmonized System (HS) code	84439990

5014047600517

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date