

Epson Expression Premium XP-6100 Inkjet A4 5760 x 1440 DPI 32 ppm Wi-Fi



Brand : Epson

Product family: Expression

Product code: C11CG97401

Product name : XP-6100

- Compact all-in-one: Print, scan and copy
- Mobile printing: Freedom to print and scan from almost anywhere
- Wi-Fi and Wi-Fi Direct: Wireless printing with or without a network
- Dual front-loading paper trays: One for A4 and another for photo paper
- A4 double-sided printing: Save paper and the environment

Expression Premium XP-6100, Micro Piezo, 5760x1440 DPI, CIS, USB, Wi-Fi, SD, AC 100-240 V, 349x340x142 mm

Epson Expression Premium XP-6100. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 5760 x 1440 DPI, Print speed (colour, normal quality, A4/US Letter): 32 ppm. Copying: Colour copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 4800 DPI. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black

Printing		Network	
Duplex printing mode	Auto	Wi-Fi *	✓
Print technology *	Inkjet	Ethernet LAN *	✗
Printing *	Colour printing	Security algorithms	64-bit WEP, 128-bit WEP, AES, TKIP, WPA-PSK
Duplex printing *	✓	Online services supported	Facebook
Maximum resolution *	5760 x 1440 DPI	Mobile printing technologies	Apple AirPrint, Epson Connect, Epson Email Print, Epson Remote Print, Epson iPrint, Google Cloud Print
Print speed (black, normal quality, A4/US Letter) *	32 ppm	Performance	
Print speed (colour, normal quality, A4/US Letter)	32 ppm	Card reader integrated	✓
Print speed (ISO/IEC 24734) mono	15.8 ipm	Compatible memory cards	SD, SDHC, SDXC
Print speed (ISO/IEC 24734) colour	11.3 ipm	Design	
Print margins (top, bottom, right, left)	0 mm	Product colour *	Black
Copying		Market positioning *	Home & office
Copying *	Colour copying	Built-in display *	✓
Scanning		Colour display	✓
Scanning *	Colour scanning	Power	
Optical scanning resolution *	1200 x 4800 DPI	Power consumption (copying)	18 W
Scan technology	CIS	Power consumption (ready)	6 W
Scan to	Cloud	Power consumption (sleep)	0.6 W
Fax		Power consumption (off)	0.2 W
Faxing *	✗	AC input voltage	100 - 240 V
Features		AC input frequency	50 - 60 Hz
Digital sender	✗	System requirements	
Printing colours *	Black, Cyan, Magenta, Photo black, Yellow	Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP
Input & output capacity		Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Total number of input trays *	2	Sustainability	
Total input capacity *	120 sheets	Sustainability certificates	ENERGY STAR
Paper input type	Paper tray		
Paper handling			
Maximum ISO A-series paper size *	A4		
Paper tray media types *	Envelopes, Photo paper, Plain paper		
ISO A-series sizes (A0...A9) *	A4, A5, A6		
ISO B-series sizes (B0...B9)	B5		
ISO C-series sizes (C0...C9)	C6		

Paper handling		Weight & dimensions	
Non-ISO print media sizes	Legal, Letter	Width	349 mm
Envelopes sizes	10, C6, DL	Depth	340 mm
Ports & interfaces		Height	142 mm
Standard interfaces	USB, Wireless LAN	Weight	6.6 kg
Direct printing *	✓	Packaging content	
USB port	✓	Cartridge(s) included	✓
		Manual	✓
		Power cord included	✓
		Warranty card	✓
		Bundled software	Epson Easy Photo Print, Epson Print CD, Epson Scan
Logistics data			
		Harmonized System (HS) code	84433100
Other features			
		PictBridge	✓
		Software CD	✓



8715946653648

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.