

Epson Expression Premium XP-7100 Inkjet A4 5760 x 1440 DPI 32 ppm Wi-Fi



Brand : Epson

Product family: Expression

Product code: C11CH03401

Product name : XP-7100

- Compact wireless all-in-one: Print, scan, copy
- Mobile printing: Freedom to print and scan from almost anywhere
- Automatic Document Feeder: Scan and copy multiple documents
- Flexible paper trays: Two front-loading trays and a rear feed
- 10.9cm interactive touchscreen: Easy navigation and PC-free photo printing from a memory card

Expression XP-7100, Micro Piezo, A4, 5760x1440 DPI, 32 pages/min, CIS, SD/SDHC/SDXC, Wi-Fi, LAN, USB, AC 220-240 V, 390x339x183 mm

Epson Expression Premium XP-7100. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 5760 x 1440 DPI, Print speed (colour, normal quality, A4/US Letter): 32 ppm. Copying: Colour copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 4800 DPI. Maximum ISO A-series paper size: A4. Wi-Fi. Direct printing. Product colour: Black

Printing		Network	
Duplex printing mode	Auto	Wi-Fi *	✓
Print technology *	Inkjet	Ethernet LAN *	✓
Printing *	Colour printing	Security algorithms	64-bit WEP, 128-bit WEP, AES, TKIP, WPA-PSK, WPA2-PSK
Duplex printing *	✓	Mobile printing technologies	Apple AirPrint, Epson Connect, Epson iPrint, Google Cloud Print
Maximum resolution *	5760 x 1440 DPI	Performance	
Print speed (black, normal quality, A4/US Letter) *	32 ppm	Card reader integrated	✓
Print speed (colour, normal quality, A4/US Letter)	32 ppm	Compatible memory cards	SD, SDHC, SDXC
Print speed (ISO/IEC 24734) mono	15.8 ipm	Design	
Print speed (ISO/IEC 24734) colour	11 ipm	Product colour *	Black
Print margins (top, bottom, right, left)	0 mm	Market positioning *	Home & office
Copying		Built-in display *	✓
Copying *	Colour copying	Display	LCD
Scanning		Touchscreen	✓
Scanning *	Colour scanning	Control type	Touch
Optical scanning resolution *	1200 x 4800 DPI	Colour display	✓
Scanner type *	ADF scanner	Power	
Scan technology	CIS	Power consumption (copying)	16 W
Fax		Power consumption (ready)	8.7 W
Faxing *	✗	Power consumption (sleep)	1.2 W
Features		Power consumption (off)	0.4 W
Digital sender	✗	AC input voltage	220 - 240 V
Printing colours *	Black, Cyan, Magenta, Photo black, Yellow	AC input frequency	50 - 60 Hz
Input & output capacity		System requirements	
Total number of input trays *	2	Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP
Total input capacity *	120 sheets	Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Paper input type	Paper tray		
Auto document feeder (ADF)	✓		
Auto document feeder (ADF) input capacity	30 sheets		
Paper handling		Sustainability	
Maximum ISO A-series paper size *	A4	Sustainability certificates	ENERGY STAR
Paper tray media types *	Envelopes, Glossy paper, Photo paper, Plain paper		

Paper handling		Weight & dimensions	
ISO A-series sizes (A0...A9) *	A4, A5, A6	Width	390 mm
ISO B-series sizes (B0...B9)	B5	Depth	339 mm
ISO C-series sizes (C0...C9)	C6	Height	183 mm
Non-ISO print media sizes	Letter	Weight	8.2 kg
Envelopes sizes	10, C6, DL	Packaging content	
Ports & interfaces		Cartridge(s) included	✓
Standard interfaces	Ethernet, USB, Wireless LAN	Manual	✓
Direct printing *	✓	Power cord included	✓
USB port	✓	Warranty card	✓
		Bundled software	Epson Easy Photo Print, Epson Print CD, Epson Scan
		Logistics data	
		Harmonized System (HS) code	84433100
		Other features	
		PictBridge	✓
		Software CD	✓



8715946651859

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.