BenQ PW30U Interactive kit

Brand : BenQ

Product code: 5A.JJR26.20E

Product name : PW30U

- Inspiration and Collaboration with BenQ Interactive Touch Technology
- PointWrite™ kit coupled with QWrite™ software to seamlessly integrate with BenQ projectors for a truly collaborative learning environment
- Compatible with Windows®/Mac* OSX operating systems

PointWrite Kit PW30U for MW855UST+ / MH856UST+
BenQ PW30U. Product type: Interactive kit, Brand compatibility: Benq, Product colour: Black. Connectivity technology: Wired & Wireless, Host interface: USB, USB connector type: Mini-USB. Battery type: AAA, Number of batteries included: 2 pc(s). Windows operating systems supported: Windows 10, Windows 7, Windows 8, Mac operating systems supported: Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High.... Width: 118.3 mm, Depth: 31.3 mm, Height: 23.6 mm

Features	
Product type *	Interactive kit
Brand compatibility *	Benq
Product colour	Black
Compatibility	MW855UST+, MH856UST+
Ports & interfaces	
Connectivity technology	Wired & Wireless
Host interface	USB
USB connector type	Mini-USB
Power	
Battery type	AAA
Number of batteries included	2 pc(s)
Software	
Windows operating systems supported	Windows 10, Windows 7, Windows 8

Software	
Mac operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur
Weight & dimensions	
Width	118.3 mm
Depth	31.3 mm
Height	23.6 mm
Weight	53 g
Packaging content	
Number of stylus pens	1
Operational conditions	
Operating temperature (T-T)	5 - 40 °C
Operating relative humidity (H-H)	10 - 85%
Logistics data	
Harmonized System (HS) code	85299097

4718755077555

0840046034689

840046034689

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date