

StarTech.com 2U Rack Blank Panel for 19in Server Racks and Cabinets

Brand : StarTech.com

Product code: BLANKB2

Product name : 2U Rack Blank Panel for 19in Server Racks and Cabinets



StarTech.com 2U Rack Blank Panel for 19in Server Racks and Cabinets

StarTech.com 2U Rack Blank Panel for 19in Server Racks and Cabinets:

Improve the cooling flow and appearance of your racks and cabinets by filling the gaps between equipment

The BLANKB2 2U Rack Blank Panel for 19in Server Racks and Cabinets is designed to EIA RS-310-C specifications and fits all 19" standard server racks and cabinets.

Ideal for improving airflow within the rack by covering the unused spaces, the filler panel/blank panel is constructed of cold-rolled steel and features a black powder coated finish that matches most industry standard black server cabinets and racks.

The StarTech.com Advantage

- Low cost individual units means you can buy exactly the right number for your rack needs
StarTech.com 2U Rack Blank Panel for 19in Server Racks and Cabinets. Type: Blank panel, Housing material: Steel, Product colour: Black. Weight: 479.9 g



Features		Packaging data	
Type *	Blank panel	Package depth	494 mm
Product colour *	Black	Package height	21 mm
Housing material	Steel	Package weight	545 g
Rack capacity	2U	Packaging content	
Compliance industry standards	EIA RS310-C	Screws included	✓
Certification	CE, REACH	Screw type	M6
Weight & dimensions		Nuts included	✓
Size (imperial) *	48.3 cm (19")	Technical details	
Weight	479.9 g	Compliance certificates	RoHS
Packaging data		Logistics data	
Package width	101 mm	Harmonized System (HS) code	85389099



0065030837651



065030837651



4058829139285

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.