

ASUS BE24EQSK computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD Black

Brand : ASUS

Product code: 90LM05M1-B09370

Product name : BE24EQSK

- Integrated Full HD webcam, mic array and stereo speakers for video conferencing and online learning
 - 23.8-inch Full HD(1920x1080) frameless IPS panel with wide viewing angles
 - Extensive connectivity with DisplayPort, HDMI, D-sub, Audio in, Earphone jack for the most flexibility
 - Ergonomic design with +35° ~ -5° tilt, ±180° swivel, ±90° pivot and 130mm height adjustments for a comfortable viewing experience
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- 24 inch (23.8 inch viewable), Full HD, IPS, Frameless, Full HD Webcam, Mic Array, Stereo Speakers, Ergonomic Design, HDMI, Eye Care, Low Blue Light, Flicker Free, Wall Mountable



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	Headphone out *	✓
Display resolution *	1920 x 1080 pixels	HDCP	✓
HD type *	Full HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Panel type *	IPS	Panel mounting interface	100 x 100 mm
Backlight type	LED	Cable lock slot *	✓
Touchscreen *	✗	Cable lock slot type	Kensington
Display brightness (typical)	300 cd/m²	Height adjustment *	✓
Response time *	5 ms	Adjustable height (max)	13 cm
Anti-glare screen	✓	Pivot	✓
Screen shape *	Flat	Pivot angle	-90 - 90°
Contrast ratio (typical) *	1000:1	Swivelling	✓
Maximum refresh rate *	75 Hz	Swivel angle range	-180 - 180°
Viewing angle, horizontal	178°	Tilt adjustment	✓
Viewing angle, vertical	178°	Tilt angle range	-5 - 35°
Display number of colours *	16.7 million colours	Power	
Performance		Energy efficiency class (SDR) *	F
NVIDIA G-SYNC *	✗	Energy consumption (SDR) per 1000 hours *	22 kWh
AMD FreeSync *	✗	Power consumption (off)	0 W
Low Blue Light technology	✓	Power consumption (PowerSave)	0.5 W
Multimedia		AC input voltage	100 - 240 V
Number of speakers	2	AC input frequency	50/65 Hz
RMS rated power	4 W	Energy efficiency scale	A to G
Built-in speaker(s) *	✓	Weight & dimensions	
Megapixel (approx.)	2 MP	Width (with stand)	540 mm
Built-in microphone	✓	Depth (with stand)	211 mm
Built-in camera *	✓		

Design		Weight & dimensions	
Product colour *	Black	Height (with stand)	362 mm
Ports & interfaces		Weight (with stand)	5.6 kg
Built-in USB hub *	✗	Width (without stand)	540 mm
VGA (D-Sub) ports quantity	1	Depth (without stand)	53 mm
DVI port	✗	Height (without stand)	355 mm
HDMI *	✓	Weight (without stand)	3.7 kg
HDMI ports quantity	1	Packaging data	
HDMI version	1.4	Package width	631 mm
DisplayPorts quantity	1	Package depth	220 mm
DisplayPort version	1.2	Package height	450 mm
Audio input	✓	Package weight	7.9 kg



4718017961271

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.