

Samsung SR65 computer monitor 61 cm (24") 1920 x 1080 pixels Full HD LED Black

Brand : Samsung

Product code: LS24R650FDUXXU

Product name : SR65

- Screen: 1920x1080 Resolution, IPS Panel
 - Technology: 5MS Response Time, 75Hz Refresh Rate, FreeSync
 - Connections: HDMI, Display Port, D-SUB, USB-Hub, Audio In, Headphone
 - Great For: Gaming and Productivity
 24" SR65 Full HD Monitor, 1920 x 1080 px, 16:9, IPS, 250 cd/m², 5ms, 75 Hz, 178°/178°, AMD FreeSync, USB, VGA, HDMI, DisplayPort, 18 kWh, E
 Samsung SR65. Display diagonal: 61 cm (24"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in USB hub, USB hub version: 2.0 / 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	61 cm (24")	VESA mounting *	✓
Display resolution *	1920 x 1080 pixels	Panel mounting interface	100 x 100 mm
HD type *	Full HD	Height adjustment *	✓
Native aspect ratio *	16:9	Adjustable height (max)	13.5 cm
Display technology *	LED	Pivot	✓
Panel type *	IPS	Pivot angle	-2 - 92°
Touchscreen *	✗	Swivelling	✓
Display brightness (typical)	250 cd/m²	Swivel angle range	-45 - 45°
Response time *	5 ms	Tilt adjustment	✓
Screen shape *	Flat	Tilt angle range	-5 - 24°
Contrast ratio (typical) *	1000:1		
Dynamic contrast ratio marketing name	Mega Contrast		
Maximum refresh rate *	75 Hz		
Viewing angle, horizontal	178°		
Viewing angle, vertical	178°		
Display number of colours *	16.7 million colours		
Display diagonal (metric)	60.4 cm		
NTSC coverage (typical)	72%		
Performance		Power	
AMD FreeSync *	✓	Energy efficiency class (SDR) *	E
AMD FreeSync type	FreeSync	Energy consumption (SDR) per 1000 hours *	18 kWh
Game mode	✓	Power consumption (typical) *	18 W
		Power consumption (standby) *	0.4 W
		Power consumption (max)	40 W
		Power consumption (off)	0.3 W
		AC input voltage	100 - 240 V
		Energy efficiency scale	A to G
Multimedia		Weight & dimensions	
Built-in speaker(s) *	✗	Width (with stand)	539.4 mm
		Depth (with stand)	200.5 mm
		Height (with stand)	473.8 mm
		Weight (with stand)	5.1 kg
		Width (without stand)	539.4 mm
		Depth (without stand)	71.6 mm
		Height (without stand)	319.7 mm
		Weight (without stand)	3.3 kg
Design		Packaging data	
Market positioning *	Business	Package width	605 mm
Product colour *	Black	Package depth	385 mm
Colour name	DARK BLUE GRAY		
Ports & interfaces			
Built-in USB hub *	✓		
USB hub version	2.0 / 3.2 Gen 1 (3.1 Gen 1)		

Ports & interfaces		Packaging data	
USB Type-A downstream ports quantity	4	Package height	215 mm
VGA (D-Sub) ports quantity	1	Package weight	6.7 kg
HDMI *	✓	Packaging content	
HDMI ports quantity	1	Cables included	AC, HDMI, USB
HDMI version	1.4	Sustainability	
DisplayPorts quantity	1	Sustainability certificates	ENERGY STAR
DisplayPort version	1.2	Logistics data	
Audio input	✓	Harmonized System (HS) code	85285210
Headphone out *	✓		



8806092084186

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.