



Canon PIXMA G550 photo printer Inkjet 4800 x 1200 DPI 8" x 10" (20x25 cm) Wi-Fi



Brand : Canon

Product family: PIXMA

Product code: 4621C008

Product name : G550

- Six dye-based inks
- Wireless printing
- 2 line LCD
- Rear feeding capacity
- Borderless photo printing
- Print only
- High page yield

LCD, Wi-Fi IEEE802.11 b/g/n/a, 50.5 dB, 445 x 564 x 249 mm, 5.1 kg

Canon PIXMA G550 photo printer Inkjet 4800 x 1200 DPI 8" x 10" (20x25 cm) Wi-Fi:

The Canon PIXMA G550 is perfect for printing large volumes of high-quality borderless photos up to A4 size in a studio, at home or in the office. Total cost of ownership is reduced with this high-volume printer thanks to the six refillable dye-based ink tanks that last longer between refills. When the time comes to change inks, the process is error-free and mess-free thanks to the non-squeeze bottles with mechanical ID. The maintenance cartridge is also simple to replace at home or in the studio, minimising downtime on busy days. You'll save time as you can print from your phone or tablet using the Canon PRINT App, Mopria or AirPrint, or connect via Wi-Fi to your devices.

Printing		Ports & interfaces	
Borderless printing *	✓	USB 2.0 ports quantity	1
Duplex printing	✓	USB connector	USB Type-B
Duplex printing mode	Manual	Network	
Print technology *	Inkjet	Wi-Fi *	✓
Maximum resolution *	4800 x 1200 DPI	Performance	
Print speed (10x15 cm)	47 s	Sound power level (printing)	50.5 dB
Print speed (colour, draft quality, A4/US Letter)	3.9 ppm	Power	
Features		Power source *	AC
Market positioning *	Home & office	Power consumption (printing) *	14 W
Product colour *	Black	Power consumption (standby)	1.2 W
Number of print cartridges	6	Power consumption (off)	0.2 W
Printing colours	Black, Cyan, Grey, Magenta, Red, Yellow	AC input voltage	100 - 240 V
Built-in display	✓	AC input frequency	50 - 60 Hz
Display	LCD	System requirements	
Control type	Buttons	Windows operating systems supported	Windows 10, Windows 7, Windows 8.1
Paper handling		Mac operating systems supported	Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina
Maximum print size *	8" x 10" (20x25 cm)	Other operating systems supported	Android, iOS
Paper tray media types	Glossy paper, High resolution paper, Iron-On Transfers, Matte paper, Photo paper, Plain paper, Rough paper, Semi-glossy paper	Operational conditions	
Maximum ISO A-series paper size	A4	Operating temperature (T-T)	5 - 35 °C
ISO A-series sizes (A0...A9)	A4, A5, A6	Operating relative humidity (H-H)	10 - 90%
ISO B-series sizes (B0...B9)	B5	Weight & dimensions	
Envelopes sizes	C5, Com-10, DL, Monarch	Width	445 mm
Borderless printing media sizes	8.9x8.9, 10x15, 13x18, 20x25	Depth	340 mm
Photo paper sizes (imperial)	3.5x3.5, 5x7, 7x10, 8x10	Height	146 mm
Ports & interfaces		Weight	5.1 kg
Direct printing *	✓	Logistics data	
PictBridge *	✓	Harmonized System (HS) code	84433210

Ports & interfaces

USB port * 



4549292172942

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.