

ASUS ProArt PA32UCG-K computer monitor 81.3 cm (32") 3840 x 2160 pixels 4K Ultra HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM03H0-B05370

Product name : PA32UCG-K

32" IPS 3840x2160, Non-Glare, 1000cd/m², 1000:1, 5ms, 120Hz, HLG/HDR10/Dolby Vision, Flicker-free, 2x 3W, 55W, VESA 100x100, 14.64 Kg
 ASUS ProArt PA32UCG-K. Display diagonal: 81.3 cm (32"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 2.0 / 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	81.3 cm (32")	USB Power Delivery up to	60 W
Display resolution *	3840 x 2160 pixels	DVI port	✗
HD type *	4K Ultra HD	HDMI *	✓
Native aspect ratio *	16:9	HDMI ports quantity	3
Display technology *	LED	HDMI version	2.0/2.1
Panel type *	IPS	DisplayPorts quantity	1
Touchscreen *	✗	DisplayPort version	1.4
Display brightness (typical)	1000 cd/m²	Thunderbolt 3 ports quantity	2
Response time *	5 ms	Audio input	✗
Display surface	Matt	Headphone out *	✓
Anti-glare screen	✓	Headphone outputs	1
Screen shape *	Flat	Headphone connectivity	3.5 mm
Supported graphics resolutions	1920 x 1080 (HD 1080), 2560 x 1440, 3840 x 2160	Charging port type	USB Type-C
Supported video modes	1080p, 1440p, 2160p	Ergonomics	
Aspect ratio	4:3, 16:9	VESA mounting *	✓
Contrast ratio (typical) *	1000:1	Panel mounting interface	100 x 100 mm
Contrast ratio (dynamic)	1000000:1	Cable lock slot *	✓
Dynamic contrast ratio marketing name	SmartContrast	Cable lock slot type	Kensington
Maximum refresh rate *	120 Hz	Height adjustment *	✓
Viewing angle, horizontal	178°	Adjustable height (max)	13 cm
Viewing angle, vertical	178°	Pivot	✓
Display number of colours *	1.073 billion colours	Pivot angle	-90 - 90°
Pixel pitch	0.1845 x 0.1845 mm	Swivelling	✓
High Dynamic Range (HDR) supported	✓	Swivel angle range	-90 - 90°
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10), Hybrid Log-Gamma (HLG)	Tilt adjustment	✓
Colour gamut standard	sRGB	Power	
sRGB coverage (typical)	100%	Energy efficiency class (SDR) *	G
Adobe RGB coverage	99.5%	Energy efficiency class (HDR) *	G
Performance		Energy consumption (SDR) per 1000 hours *	60 kWh
NVIDIA G-SYNC *	✗	Energy consumption (HDR) per 1000 hours *	60 kWh

Performance		Power	
AMD FreeSync *	✓	Power consumption (typical) *	55 W
AMD FreeSync type	FreeSync Premium Pro	Power consumption (off)	0 W
Flicker-free technology	✓	Power consumption (PowerSave)	0.5 W
Low Blue Light technology	✓	AC input voltage	100 - 240 V
Multimedia		AC input frequency	50 - 60 Hz
Number of speakers	2	Energy efficiency scale	A to G
RMS rated power	3 W	Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	727 mm
Built-in camera *	✗	Depth (with stand)	240 mm
Design		Height (with stand)	470 mm
Market positioning *	Graphics design	Weight (with stand)	14.6 kg
Product colour *	Black	Width (without stand)	727 mm
Frameless design	✓	Depth (without stand)	93 mm
Front bezel colour	Grey	Height (without stand)	426 mm
Detachable stand	✓	Weight (without stand)	9.7 kg
Feet colour	Black	Packaging data	
Ports & interfaces		Package width	923 mm
Built-in USB hub *	✓	Package depth	386 mm
USB hub version	2.0 / 3.2 Gen 1 (3.1 Gen 1)	Package height	525 mm
USB upstream port type	USB Type-C	Package weight	19.8 kg
Number of upstream ports	1	Package type	Box
Number of USB Type-C upstream ports quantity	1	Packaging content	
USB Type-A downstream ports quantity	3	Stand included	✓
		Logistics data	
		Harmonized System (HS) code	85285210



0195553016469



195553016469



4711081016427



4711081016458

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.