

Epson WorkForce DS-770II Sheet-fed scanner 600 x 600 DPI A3
Black, White

Brand : Epson Product family: WorkForce Product code: B11B262401BY
Product name : DS-770II

- Scan Speed 45ppm/90ipm
 - Scan up to A3
 - Scan from 27gsm to 413gsm
 - One Pass Duplex Scanning
- A3, ReadyScan LED, 600 DPI x 600 DPI, USB 3.0

Epson WorkForce DS-770II Sheet-fed scanner 600 x 600 DPI A3 Black, White:



THE HIGH-SPEED A4 SCANNER FOR EASY INTEGRATION IN BUSY WORKGROUPS

Built for high-demand environments, the WorkForce DS-770II delivers high-quality scans at up to 45 ppm / 90 ipm. The daily duty cycle of up to 7,000 sheets keeps productivity on the floor, always at its peak. The DS-770II can easily integrate into an organisation's existing document management system. A robust 100-page Auto Document Feeder and a range of media handling options make this heavy-duty scanner perfect for any organisation.

Scanning		Performance	
Maximum scan size *	215.9 x 6096 mm	Light source	ReadyScan LED
Optical scanning resolution *	600 x 600 DPI	Scan file formats	BMP, JPEG, PNG
Duplex scanning *	✓	Daily duty cycle (max) *	7000 pages
Input colour depth	30 bit	Scan to	E-mail, FTP, Network folder, Print
Output colour depth	24 bit	Scan drivers	ISIS, TWAIN, WIA
Output monochrome depth	8 bit	Paper handling	
Design		Maximum ISO A-series paper size *	A3
Scanner type *	Sheet-fed scanner	Paper tray media weight	27 - 413 g/m ²
Product colour *	Black, White	Ports & interfaces	
Built-in display *	✗	USB port *	✓
Performance		USB version	2.0/3.2 Gen 1 (3.1 Gen 1)
Sensor type *	CIS		



8715946685977

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.