



D-Link QSFP+, 3m InfiniBand/fibre optic cable QSFP+ Black

Brand : D-Link

Product code: DEM-CB300QXS

Product name : QSFP+, 3m

40G Passive QSFP+ Twinaxial Direct Attach Cable, 3m

D-Link QSFP+, 3m InfiniBand/fibre optic cable QSFP+ Black:

The 40G Passive QSFP+ Twinaxial Direct Attach Cable is a high performance, high bandwidth and cost-effective connection solution that supports 40G Gigabit Ethernet. The 40G Passive QSFP+ Twinaxial Direct Attach Cable is designed to support high-density connections for switches with 40G interface, much faster than SFP+. There are three cable models, including the DEM-CB100QXS (one meter) and the DEM-CB300QXS (three meter). The DEM-CB100QXS-4XS QSFP+ to 4X SFP+ one-meter cable features a QSFP+ connector on one end, and four SFP+ connectors on the other end, allowing it to connect to up to four 10G servers. The 40G Passive QSFP+ Twinaxial Direct Attach Cable is certified to be compatible with D-Link products to provide you best performance and reliability.

D-Link QSFP+, 3m. Cable length: 3 m, Connector 1: QSFP+, Connector 2: QSFP+



Features		Logistics data	
Cable length *	3 m	Master (outer) cases per pallet (air)	30 pc(s)
InfiniBand protocol	✓	Products per pallet (air)	300 pc(s)
Connector 1 *	QSFP+	Pallet height (air)	146 cm
Connector 2 *	QSFP+	Pallet gross weight (sea)	246.5 kg
Product colour *	Black	Master (outer) cases per pallet (sea)	42 pc(s)
Data transfer rate	40 Gbit/s	Products per pallet (sea)	420 pc(s)
Packaging data		Pallet height (sea)	199 cm
Package width	267 mm	Pallet gross width	120 cm
Package depth	317 mm	Pallet gross length	110 cm
Package height	46 mm	Shipping (inner) case width	33.6 cm
Package weight	456 g	Shipping (inner) case length	56.2 cm
Logistics data		Shipping (inner) case height	26.5 cm
Shipping (inner) case net weight	4.56 kg	Shipping (inner) case gross weight	5.56 kg
Pallet gross weight (air)	179.8 kg	Products per shipping (inner) case	10 pc(s)



0790069390197



790069390197

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.