



BenQ LU930 Standard throw projector 5000 ANSI lumens DLP WUXGA (1920x1200) White

Brand : BenQ

Product code: 9H.JM277.15E

Product name : LU930

- Let Your Innovation Shine through Accurate True Color

- 3,000,000:1 contrast ratio

- 92% Rec.709 color coverage

- IP5X dustproof mechanism reducing maintenance costs

DLP, 0.48", WUXGA (1920 x 1200), 16:10, 5000 lm, HDMI, D-sub, RS232, LAN, USB, 416 x 166 x 351 mm

BenQ LU930. Projector brightness: 5000 ANSI lumens, Projection technology: DLP, Projector native resolution: WUXGA (1920x1200). Light source type: Laser, Service life of light source: 20000 h. Focus: Manual, Zoom ratio: 1.6:1, Throw ratio: 1.36 ~ 2.18. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 480 (VGA), 1920 x 1200 (WUXGA), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size, HDMI version: 1.4a



Projector		Ports & interfaces	
Supported aspect ratios	16:10	AC (power) in	✓
Screen size compatibility *	762 - 7620 mm (30 - 300")	Network	
Projector brightness *	5000 ANSI lumens	Smart TV *	✗
Projection technology *	DLP	Ethernet LAN *	✓
Projector native resolution *	WUXGA (1920x1200)	Ethernet LAN (RJ-45) ports	1
Contrast ratio (typical) *	3000000:1	Wi-Fi *	✗
Native aspect ratio *	16:10	Storage	
Number of colours	1.073 billion colours	Card reader integrated *	✗
Horizontal scan range	15 - 102 kHz	Features	
Vertical scan range	23 - 120 Hz	Noise level (economic mode)	30 dB
Keystone correction, horizontal	-30 - 30°	On Screen Display (OSD)	✓
Keystone correction, vertical	-30 - 30°	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish, Vietnamese
Matrix size	1.22 cm (0.48")	Number of OSD languages	30
Matrix type	DMD	Noise level *	37 dB
Light source		Multimedia	
Light source type *	Laser	Built-in speaker(s) *	✓
Service life of light source *	20000 h	RMS rated power	20 W
Lens system		Number of built-in speakers	2
Focus *	Manual	Design	
Zoom capability	✓	Market positioning *	Business
Zoom ratio	1.6:1		
Throw ratio	1.36 ~ 2.18		
Horizontal lens shift range	-23 - 23%		
Vertical lens shift range	-60 - 60%		
Video			
Analog signal format system *	NTSC, PAL, SECAM		
Full HD *	✓		

Video		Design	
3D *	✗	Product type *	Standard throw projector
Supported graphics resolutions	640 x 480 (VGA), 1920 x 1200 (WUXGA)	Product colour *	White
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p	Placement	Desktop, Ceiling
Ports & interfaces		Cable lock slot	✓
HDMI connector type	Full-size	Cable lock slot type	Kensington
HDMI version	1.4a	Display	
USB 2.0 ports quantity	1	Built-in display *	✗
Audio (L/R) in *	1	Power	
Serial interface type *	RS-232	Power source *	AC
PC Audio in	✓	Power consumption (typical) *	415 W
PC Audio out	✓	Power consumption (standby) *	0.5 W
PC in (D-Sub)	✓	Power consumption (max)	475 W
VGA (D-Sub) ports quantity *	1	AC input voltage	100 - 240 V
HDMI ports quantity *	2	Operational conditions	
Composite video in *	1	Operating temperature (T-T)	0 - 40 °C
Component video (YPbPr/YCbCr) in *	1	Weight & dimensions	
DVI port *	✗	Width	416 mm
		Depth	351 mm
		Height	166 mm
		Weight *	6.3 kg
		Packaging content	
		Remote control included *	✓
		Batteries included	✓
		Cables included	AC, HDMI
		Logistics data	
		Quantity per pack	1 pc(s)
		Harmonized System (HS) code	85286200



4718755080647

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.