



APC Smart-UPS SRT 48V 1kVA 1.5kVA Battery Pack

Brand : APC
Product code: SRT48BP
Product name : Smart-UPS SRT 48V 1kVA 1.5kVA Battery Pack

Smart-UPS SRT 48V 1kVA 1.5kVA Battery Pack

APC Smart-UPS SRT 48V 1kVA 1.5kVA Battery Pack:

This product is part of the Smart-UPS battery systems, providing extended runtime to SRT mission critical applications. This extendable-run battery pack provides extended runtime during prolonged power outages. Embedded monitoring at the cell, module, and cabinet level provides data of battery runtime and health. It is a lead-acid battery with a 2-year warranty. Its dimensions are 536mm (depth) x 432mm (height) x 85mm (width) and weighs 29.9kg. Ideal for Smart-UPS on-line mission critical applications.


APC Smart-UPS SRT 48V 1kVA 1.5kVA Battery Pack. Output power capacity: 1.5 kVA. Battery technology: Sealed Lead Acid (VRLA), Battery life (max): 5 year(s). Form factor: Tower, Product colour: Black. Width: 85 mm, Depth: 536 mm, Height: 432 mm. Package width: 594 mm, Package depth: 749 mm, Package height: 244 mm



Features		Packaging content	
Output power capacity *	1.5 kVA	Manual	✓
Battery		Weight & dimensions	
Battery technology	Sealed Lead Acid (VRLA)	Width	85 mm
Battery life (max)	5 year(s)	Depth	536 mm
Hot-swap battery	✓	Height	432 mm
Design		Weight	29.9 kg
Form factor *	Tower	Packaging data	
Product colour *	Black	Package width	594 mm
Operational conditions		Package depth	749 mm
Operating temperature (T-T)	0 - 40 °C	Package height	244 mm
Storage temperature (T-T)	-15 - 45 °C	Package weight	37 kg
Operating relative humidity (H-H)	0 - 95%	Logistics data	
Storage relative humidity (H-H)	0 - 95%	Products per pallet	6 pc(s)
Operating altitude	0 - 3000 m	Harmonized System (HS) code	85078000
Non-operating altitude	0 - 15000 m	Other features	
		Output voltage	48 V



0731304330141



731304330141

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.