

Epson WorkForce DS-360W ADF scanner 600 x 600 DPI A4 Black

Brand : Epson

Product family: WorkForce

Product code: B11B242401PU

Product name : DS-360W

A4 Scanner, 1200 x 1200dpi, USB 3.0, WLAN

Epson WorkForce DS-360W. Maximum scan size: 215.9 x 1117.6 mm, Optical scanning resolution: 600 x 600 DPI, Input colour depth: 48 bit. Scanner type: ADF scanner, Product colour: Black. Sensor type: CIS, Daily duty cycle (max): 500 pages, Light source: RGB LED. Auto document feeder (ADF) input capacity: 20 sheets. Maximum ISO A-series paper size: A4, Scanning media types supported: Envelopes, ISO A-series sizes (A0...A9): A4, A5, A6



Scanning		Ports & interfaces	
Maximum scan size *	215.9 x 1117.6 mm	USB port *	✓
Optical scanning resolution *	600 x 600 DPI	USB version	3.2 Gen 1 (3.1 Gen 1)
Colour scanning	✓	USB connector type	Micro-USB
Duplex scanning *	✓	Network	
Input colour depth	48 bit	Wi-Fi	✓
Output colour depth	24 bit	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n)
Film scanning	✗	Power	
ADF scan speed (b/w, A4)	25 ppm	Power supply type *	AC
ADF scan speed (colour, A4)	25 ppm	Weight & dimensions	
Design		Width	288 mm
Scanner type *	ADF scanner	Depth	89 mm
Product colour *	Black	Height	67 mm
Built-in display *	✗	Weight	1.3 kg
Performance		Packaging data	
Sensor type *	CIS	Quantity per pack	1 pc(s)
Light source	RGB LED	Package width	120 mm
Scan file formats	BMP, JPG, PDF, TIFF	Package depth	385 mm
Daily duty cycle (max) *	500 pages	Package height	140 mm
Scan to	E-mail, FTP	Package weight	1.94 g
Scan drivers	TWAIN	Packaging content	
Input capacity		Cables included	AC, USB
Auto document feeder (ADF) input capacity	20 sheets	Sustainability	
Paper handling		Sustainability certificates	ENERGY STAR
Scanning media types supported	Envelopes	Operational conditions	
Maximum ISO A-series paper size *	A4	Operating temperature (T-T)	5 - 35 °C
ISO A-series sizes (A0...A9)	A4, A5, A6		

Paper handling		Operational conditions	
ISO B-series sizes (B0...B9)	B5, B6	Storage temperature (T-T)	-25 - 60 °C
Letter	✓	Operating relative humidity (H-H)	15 - 80%
Legal	✓	Storage relative humidity (H-H)	15 - 85%
Auto Document Feeder (ADF) media weight	52 - 230 g/m²	Logistics data	
		Country of origin	China
		Harmonized System (HS) code	84716070

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.