DELL Pro Plus Mouse - MS5320W

Brand : DELL

Product code: MS5320W-GY

Product name : Pro Plus Mouse - MS5320W



Pro Plus Mouse - MS5320W

DELL Pro Plus Mouse - MS5320W:

Work seamlessly across your desktop, laptop and 2-in-1 with this sculpted wireless mouse.
DELL Pro Plus Mouse - MS5320W. Form factor: Right-hand. Movement detection technology: Optical, Device interface: RF Wireless + Bluetooth, Movement resolution: 1600 DPI, Buttons type: Pressed buttons, Buttons quantity: 7, Scroll type: Wheel. Power source: Batteries. Product colour: Grey, Titanium



Mouse	
Number of scroll wheels	1
Purpose *	Office
Device interface *	RF Wireless + Bluetooth
Movement detection technology *	Optical
Movement resolution *	1600 DPI
Buttons type	Pressed buttons
Scroll type *	Wheel
Programmable mouse buttons	✔
Buttons quantity *	7
Number of programmable buttons	2
Frequency band	2.4 GHz
Bluetooth version	5.0

Design	
Form factor *	Right-hand
Product colour *	Grey, Titanium
Surface coloration	Monochromatic

Ergonomics	
Wireless range	10 m

Power	
Power source *	Batteries
Number of batteries supported	1
Battery type	AA
Battery technology	Alkaline
Service life of battery	36 month(s)

System requirements	
Mac operating systems supported	✔
Linux operating systems supported	✔
Mobile operating systems supported	Android
Other operating systems supported	ChromeOS, DOS


Operational conditions	
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-40 - 65 °C

Weight & dimensions	
Width	114.5 mm
Depth	69.7 mm
Height	41.6 mm
Weight	84 g

Packaging data	
Quantity per pack *	1 pc(s)
Package width	87.5 mm
Package depth	53 mm
Package height	160 mm
Package weight	185 g

Packaging content	
Receiver included	✔

Logistics data	
Harmonized System (HS) code	84716070




5397184289037



0884116366171




884116366171



5704174224976



0884116366362



884116366362



5715063710647

Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date