

Epson WorkForce ES-50



Brand : Epson

Product family: WorkForce

Product code: B11B252401

Product name : WorkForce ES-50

- Scan anywhere: Small, lightweight design
 - USB connectivity: Powered by USB
 - Fast scanning speeds: At up to 5.5 seconds per page
 - Simplify your workload: Continuous scanning with automatic feed mode
 - Includes new ScanSmart software: Get scanning quickly and easily
- WorkForce ES-50

Epson WorkForce ES-50:

Scan anywhere

The compact design and USB connectivity make it easy to use the ES-50 wherever it's needed.

Highly organised

Epson's new ScanSmart software makes it effortless for anyone to scan how they want, providing an easy-to-use step by step scanning solution. Users can save and send files in common formats like PDF, jpeg, tiff and many more. Continuous scanning with automatic feed mode speeds up the scanning process, while the CIS sensor delivers instant scanning with no warm up time.

Flexible

The ability to scan a wide range of document and media types makes this model a reliable asset. It handles paper from 35gsm to 270gsm, and long paper up to 1.8 metres.

Scanning		Packaging content	
Optical scanning resolution *	600 x 600 DPI	Cables included	USB
Colour scanning	✓	Drivers included	✓
Duplex scanning *	✗	Bundled software	Epson Scan 2, Epson ScanSmart
Input colour depth	48 bit	System requirements	
Output colour depth	24 bit	Compatible operating systems	Mac OS 10.6+, Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Server 2003, Windows Server 2008 (32/64 Bit), Windows Server 2012 R2, Windows Server 2016, Windows Vista, Windows XP
Input greyscale depth	16 bit		Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP
Output greyscale depth	8 bit		Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Scan speed (b/w, low res, A4)	5.5 sec/page	Windows operating systems supported	Windows Server 2003, Windows Server 2008, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2016
Scan speed (colour, low res, A4)	5.5 sec/page	Mac operating systems supported	
Design		Server operating systems supported	
Scanner type *	Handheld scanner	Operational conditions	
Product colour *	Black	Operating temperature (T-T)	5 - 35 °C
Built-in display *	✗	Storage temperature (T-T)	-20 - 60 °C
Performance		Operating relative humidity (H-H)	10 - 85%
Sensor type *	CIS	Storage relative humidity (H-H)	10 - 90%
Daily duty cycle (max) *	300 pages	Other features	
Scan drivers	WIA, SANE, ICA	Output resolutions	600 dpi
Input capacity		Image formats supported	JPEG
Auto document feeder (ADF) input capacity	1 sheets	Technical details	
Paper handling		Scan technology	ReadyScan LED
Scanning media types supported	Business Card, Plastic Card, Post Card(JPN)		
Maximum ISO A-series paper size *	A4		
ISO A-series sizes (A0...A9)	A4, A5, A6, A7, A8		
ISO B-series sizes (B0...B9)	B5, B6		
Letter	✓		
Legal	✓		
Paper tray media weight	35 - 270 g/m²		

Paper handling		Logistics data	
Auto Document Feeder (ADF) media weight	35 - 270 g/m²	Products per pallet	360 pc(s)
Ports & interfaces		Country of origin	China
USB port *	✓	Pallet gross weight	0 g
USB version	2.0	Master (outer) case length	360 mm
Standard interfaces	USB 2.0	Master (outer) case height	320 mm
Power		Master (outer) case width	350 mm
Power supply type *	USB	Master (outer) case gross weight	0 g
Weight & dimensions		Pallet gross length	120 cm
Width	272 mm	Pallet gross width	80 cm
Depth	47 mm	Pallet gross height	171 cm
Height	34 mm	Products per master (outer) case	10 pc(s)
Weight	270 g	Products per pallet layer	60 pc(s)
Packaging data		Products per pallet layer (UK)	60 pc(s)
Quantity per pack	1 pc(s)	Products per pallet (UK)	360 pc(s)
Package width	140 mm	Pallet weight (UK)	0 g
Package depth	330 mm	Pallet length (UK)	120 cm
Package height	65 mm	Pallet width (UK)	100 cm
Package weight	550 g	Pallet height (UK)	171 cm
		Master (outer) case GTIN (EAN/UPC)	8715946656922
		Harmonized System (HS) code	84716070



8715946656908

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.