



BenQ MW826STH Short throw projector 3500 ANSI lumens DLP WXGA (1280x800) 3D White

Brand : BenQ

Product code: 9H.JMW77.13E

Product name : MW826STH



- 0.49 Short Throw Ratio

- SmartEco Power Saving Technology

- PointWrite Interactive Solution Compatible

DLP, 3500 ANSI Lumen, 1280 x 800, 16:10, 20000:1, RMS 10W

BenQ MW826STH. Projector brightness: 3500 ANSI lumens, Projection technology: DLP, Projector native resolution: WXGA (1280x800). Light source type: Lamp, Service life of light source: 6000 h, Service life of light source (economic mode): 10000 h. Throw ratio: 0.49:1, Offset: 105%. Supported 3D formats:

Frame Sequential, Frame packing, Side by side, Top and bottom, Supported graphics resolutions: 640 x 480 (VGA), 1920 x 1200 (WUXGA), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p.

Serial interface type: RS-232



Projector		Network	
Screen size compatibility *	1778 - 3048 mm (70 - 120")	Ethernet LAN (RJ-45) ports	1
Projector brightness *	3500 ANSI lumens	Storage	
Projection technology *	DLP	Card reader integrated *	✗
Projector native resolution *	WXGA (1280x800)	Features	
Contrast ratio (typical) *	20000:1	Interactive *	✓
Native aspect ratio *	16:10	Noise level (economic mode)	29 dB
Number of colours	1.07 billion colours	On Screen Display (OSD)	✓
Keystone correction, vertical	-30 - 30°	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish
Matrix size	1.65 cm (0.65")		
Light source		Noise level *	33 dB
Light source type *	Lamp	Multimedia	
Service life of light source *	6000 h	Built-in speaker(s) *	✓
Service life of light source (economic mode)	10000 h	RMS rated power	10 W
Lamps quantity	1 lamp(s)	Number of built-in speakers	1
Lens system		Design	
Zoom capability	✗	Market positioning *	Presentation
Throw ratio	0.49:1	Product type *	Short throw projector
Offset	105%	Product colour *	White
Video		Cable lock slot	✓
Full HD *	✗	Cable lock slot type	Kensington
3D *	✓		
Supported 3D formats	Frame Sequential, Frame packing, Side by side, Top and bottom		
Supported graphics resolutions	640 x 480 (VGA), 1920 x 1200 (WUXGA)		
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p		

Ports & interfaces		Power	
S-Video inputs quantity	1	Power source *	AC
USB 2.0 ports quantity	1	Power consumption (typical) *	260 W
Mini-USB 2.0 ports quantity	1	Power consumption (standby) *	0.5 W
Audio (L/R) in *	1	AC input voltage	100 - 240 V
Serial interface type *	RS-232	AC input frequency	50 / 60 Hz
PC Audio in	✓	Operational conditions	
PC Audio out	✓	Operating temperature (T-T)	0 - 40 °C
VGA (D-Sub) ports quantity *	3	Weight & dimensions	
HDMI ports quantity *	2	Width	296 mm
Composite video in *	1	Depth	239 mm
DVI port *	✗	Height	120 mm
AC (power) in	✓	Weight *	2.6 kg
Network		Packaging content	
Ethernet LAN *	✓	Remote control included *	✓
		Remote control type	IR
		Batteries included	✓
		Cables included	AC
		Manual	✓
		Logistics data	
		Quantity per pack	1 pc(s)
		Harmonized System (HS) code	85286200



4718755083808

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.