APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1200D mm




Brand : APC

Product code: ER6222

Product name : Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1200D mm

Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1200D mm
APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 600W x 1200D mm. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1199.75 kg, Castor wheels. Weight: 108.6 kg. Product colour: Black



Features	
Rack capacity *	42U
Type *	Freestanding rack
Maximum weight capacity *	1199.75 kg
Maximum weight capacity (rolling)	599.65 kg
Product colour	Black
Side panels included	✔
Castor wheels	✔
Preassembled	✔
Certification	EIA-310E, UL 2416, UL 60950-1
Weight & dimensions	
Size (imperial)	48.3 cm (19")
Width	600 mm

Weight & dimensions	
Depth	1200 mm
Height	1991 mm
Weight	108.6 kg
Packaging data	
Package width	1250 mm
Package depth	650 mm
Package height	2120 mm
Package weight	116 kg
Technical details	
Total carbon footprint (kg of CO2e)	351.98
Logistics data	
Harmonized System (HS) code	85381000

0731304427810

731304427810

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date