
HP 849 400-ml Cyan PageWide XL Ink Cartridge



Brand : HP

Product code: 1XB39A

Product name : 849 400-ml Cyan PageWide XL Ink Cartridge

- Produce dark blacks, vivid colors—even on uncoated bond—in moisture-, fade-resistant prints.[1] Set a new technical document standard—crisp lines, fine detail, smooth grayscales. HP PageWide XL pigment ink—fast, high-quality HP PageWide XL printing.
- High-volume production of technical documents as well as GIS map and point-of-sale (POS) poster applications.
- 1 Cartridge

849 400-ml Cyan PageWide XL Ink Cartridge



HP 849 400-ml Cyan PageWide XL Ink Cartridge:

High-volume production of technical documents as well as GIS map and point-of-sale (POS) poster applications.
Produce dark blacks, vivid colors—even on uncoated bond—in moisture-, fade-resistant prints.[1] Set a new technical document standard—crisp lines, fine detail, smooth grayscales. HP PageWide XL pigment ink—fast, high-quality HP PageWide XL printing.

Features	
Colour ink type	Pigment-based ink
Compatibility *	HP PageWide XL 3900
Quantity per pack *	1 pc(s)
Colour ink cartridges quantity	1
Colour ink volume	400 ml
Type *	Original
Cartridge capacity	Standard Yield
Ink type	Pigment-based ink
Printing colours *	Cyan
Brand compatibility *	HP
Country of origin	Singapore
Operational conditions	
Operating relative humidity (H-H)	20 - 80%
Storage temperature (T-T)	0 - 40 °C
Operating temperature (T-T)	15 - 35 °C
Weight & dimensions	
Width	54 mm
Depth	115.9 mm
Height	174.6 mm
Weight	570 g
Packaging data	
Package width	54 mm
Package depth	115.9 mm
Package height	174.6 mm
Package weight	620 g

Sustainability	
Total carbon footprint (kg of CO2e)	3
Brand-specific features	
HP GTIN (EAN/UPC)	193808308895
Other features	
UNSPSC-code	441031052
Technical details	
Box contents	1 Cartridge
Logistics data	
Pallet dimensions (W x D x H)	1016 x 1219.2 x 1110 mm
Products per pallet	1200 pc(s)
Master (outer) cases per pallet	120 pc(s)
Layers per pallet	6 pc(s)
Master (outer) cases per pallet layer	20 pc(s)
Pallet gross weight	550 kg
Products per master (outer) case	10 pc(s)
Master (outer) case gross weight	6.55 kg
Pallet dimensions (W x D x H) (imperial)	1016 x 1219.2 x 1110 mm (40 x 48 x 43.7")
Pallet weight (imperial)	372.4 kg (821 lbs)
Master (outer) case gross weight (imperial)	6.55 kg (14.4 lbs)
Harmonized System (HS) code	84439990



0193808308895



193808308895

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date