

Epson WorkForce DS-30000 Sheet-fed scanner 600 x 600 DPI A3
Black, White

Brand : Epson Product family: WorkForce Product code: B11B256401BY

Product name : DS-30000

- Space saving: Compact design without compromise on engineering quality
- Fast performance: Up to 70ppm/140ipm scanning at 200 or 300dpi colour
- Flexible scanning: Scan passports and bound media up to 6mm in thickness
- Control and security: Advanced paper handling with paper-protection sensors
- High capacity: Heavy duty 120-sheet document feeder (ADF)
70ppm, 140ipm, 600 DPI, USB 3.0, AC 100 V - 240 V
Epson WorkForce DS-30000. Maximum scan size: 304.8 x 5588 mm, Optical scanning resolution: 600 x 600 DPI, Input colour depth: 10 bit. Scanner type: Sheet-fed scanner, Product colour: Black, White, Display: LCD. Sensor type: CIS, Daily duty cycle (max): 30000 pages, Scanning noise level: 64 dB. Auto document feeder (ADF) input capacity: 120 sheets. Maximum ISO A-series paper size: A3

Scanning		Paper handling	
Maximum scan size *	304.8 x 5588 mm	Maximum ISO A-series paper size * A3	
Optical scanning resolution *	600 x 600 DPI	Ports & interfaces	
Colour scanning	✓	USB port *	✓
Duplex scanning *	✓	USB version	3.2 Gen 1 (3.1 Gen 1)
Input colour depth	10 bit	Standard interfaces	USB 3.2 Gen 1 (3.1 Gen 1)
Output colour depth	8 bit	Power	
ADF scan speed (b/w, A4)	70 ppm	Power supply type *	AC
Design		Power consumption (typical)	17 W
Scanner type *	Sheet-fed scanner	Power consumption (standby)	9 W
Product colour *	Black, White	Power consumption (off)	0.1 W
Display	LCD	Sleep mode	✓
Display diagonal	6.86 cm (2.7")	Input voltage	100 - 240 V
Built-in display *	✓	Weight & dimensions	
Performance		Width	371 mm
Sensor type *	CIS	Depth	208 mm
Daily duty cycle (max) *	30000 pages	Height	219 mm
Scanning noise level	64 dB	Weight	5.8 kg
Sound pressure level (max)	51 dB	Operational conditions	
Input capacity		Operating relative humidity (H-H)	15 - 80%
Auto document feeder (ADF) input capacity	120 sheets	Storage relative humidity (H-H)	15 - 85%
Logistics data			
		Harmonized System (HS) code	84716070



8715946676579

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.