

Epson WorkForce DS-32000 Sheet-fed scanner 600 x 600 DPI A3
Black, White

Brand : Epson

Product code: B11B255401BY

Product name : WorkForce DS-32000

- High-volume scanning: 90ppm/180ipm & 40,000 daily duty cycles
- Adjustable chassis design: Normal, Horizontal and Compact options to suit your space
- Media versatility: Scan passports and bound media up to 6mm in thickness
- Control and security: Advanced paper handling with paper-protection sensors
- A4 and A3 flatbed options: Scan books and bound media with optional flatbed scanners

90ppm, 180ipm, 40000 daily duty cycles, 300 dpi, AC 100 V - 240 V, 5.8 kg
Epson WorkForce DS-32000. Optical scanning resolution: 600 x 600 DPI, Input colour depth: 10 bit, Output colour depth: 8 bit. Scanner type: Sheet-fed scanner, Product colour: Black, White, Display: LCD. Sensor type: CIS, Daily duty cycle (max): 40000 pages. Auto document feeder (ADF) input capacity: 120 sheets. Maximum ISO A-series paper size: A3

Scanning		Ports & interfaces	
Optical scanning resolution *	600 x 600 DPI	USB version	3.2 Gen 1 (3.1 Gen 1)
Colour scanning	✓	Standard interfaces	USB 3.2 Gen 1 (3.1 Gen 1)
Duplex scanning *	✓	Power	
Input colour depth	10 bit	Power supply type *	AC
Output colour depth	8 bit	Power consumption (typical)	20 W
ADF scan speed (b/w, A4)	90 ppm	Power consumption (standby)	11 W
Design		Power consumption (off)	0.1 W
Scanner type *	Sheet-fed scanner	Sleep mode	✓
Product colour *	Black, White	Input voltage	100 - 240 V
Display	LCD	Weight & dimensions	
Display diagonal	6.86 cm (2.7")	Width	371 mm
Built-in display *	✓	Depth	208 mm
Performance		Height	219 mm
Sensor type *	CIS	Weight	5.8 kg
Daily duty cycle (max) *	40000 pages	Packaging content	
Input capacity		Manual	✓
Auto document feeder (ADF) input capacity	120 sheets	AC adapter included	✓
Paper handling		Operational conditions	
Maximum ISO A-series paper size *	A3	Operating relative humidity (H-H)	15 - 80%
Ports & interfaces		Storage relative humidity (H-H)	15 - 85%
USB port *	✓	Logistics data	
		Harmonized System (HS) code	84716070



8715946676555

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.