



APC BE650G2-SP uninterruptible power supply (UPS) Standby (Offline) 0.65 kVA 400 W 8 AC outlet(s)

Brand : APC

Product code: BE650G2-SP

Product name : BE650G2-SP

Back-UPS 650VA, 230V, 1x USB

APC BE650G2-SP. UPS topology: Standby (Offline), Output power capacity: 0.65 kVA, Output power: 400 W. AC outlet types: Type F, AC outlets quantity: 8 AC outlet(s), USB port type: USB Type-A. Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 75 Ah, Battery life (max): 5 year(s). Form factor: Compact, Product colour: Black, Cable length: 1.83 m. Compliance certificates: RoHS, Certification: CE, EAC REACH




Features		Battery	
UPS topology *	Standby (Offline)	Battery recharge time	16 h
Output power capacity *	0.65 kVA	Hot-swap battery	✓
Output power *	400 W	Automatic battery test	✓
Waveform *	Sine	Cold start	✓
Input operation voltage (min) *	180 V	Design	
Input operation voltage (max) *	266 V	Form factor *	Compact
Input frequency *	47/63 Hz	Cable length	1.83 m
Output operation voltage (min)	220 V	Product colour *	Black
Output operation voltage (max)	230 V	LED indicators	✓
Output frequency	47/63 Hz	Operational conditions	
Maximum current	6 A	Operating temperature (T-T)	0 - 40 °C
Surge energy rating	310 J	Storage temperature (T-T)	-15 - 45 °C
Efficiency	80%	Operating relative humidity (H-H)	0 - 90%
Noise level	45 dB	Storage relative humidity (H-H)	0 - 95%
Surge protection	✓	Non-operating altitude	0 - 4500 m
Surge protection features	Digital Subscriber Line (DSL), Fax, Modem, Network, Telephone	Certificates	
Audible alarm(s)	✓	Compliance certificates	RoHS
Audible alarm modes	Alarm when on battery, Low battery alarm, Overload alarm	Certification	CE, EAC REACH
Ports & interfaces		Packaging content	
AC outlet types	Type F	Manual	✓
AC outlets quantity	8 AC outlet(s)	Weight & dimensions	
Number of type F outputs	8	Width	130 mm
USB port	✓	Depth	365 mm
USB 2.0 ports quantity	1	Height	120 mm
USB port type	USB Type-A	Weight	4 kg
Modem (RJ-11) ports	2		
Ethernet LAN (RJ-45) ports	1		

Ports & interfaces		Packaging data	
Cabling technology	10/100Base-T	Package width	186 mm
Battery		Package depth	441 mm
Battery technology	Sealed Lead Acid (VRLA)	Package height	190 mm
Battery capacity	75 Ah	Package weight	4.5 kg
Battery life (max)	5 year(s)	Logistics data	
		Harmonized System (HS) code	85078000
		Master (outer) case gross weight	14.5 kg



0731304347248



731304347248

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.