PHILIPS

# Philips BS9B1617TB/00 monitor accessory Bracket

**Brand :** Philips

**Product code:** BS9B1617TB/00

**Product name :** BS9B1617TB/00



BS9B1617TB Client mounting bracket

Philips BS9B1617TB/00 monitor accessory Bracket:

Maximize desk space and secure PC clients to your Philips touch monitor with the client mounting bracket. This simple versatile solution allows you to create an All-in-One like setup for max productivity Philips BS9B1617TB/00. Product type: Bracket, Compatibility: Philips Base of 162B9T*, 172B9T*. Weight: 310 g. Product colour: Black. Quantity per pack: 1 pc(s)



| Features | |
|---|---|
| Product type * | Bracket |
| Compatibility * | Philips Base of 162B9T*, 172B9T* |
| Product colour | Black |
| Maximum weight capacity | 5 kg |
| Touchscreen | ✗ |
| Panel mounting interface | 100 x 100 mm |
| VESA mounting | ✓ |

| Weight & dimensions | |
|---|---|
| Width | 217 mm |
| Depth | 32 mm |
| Height | 128 mm |
| Weight | 310 g |

| Packaging data | |
|---|---|
| Quantity per pack | 1 pc(s) |
| Package height | 45 mm |

| Packaging data | |
|---|---|
| Package width | 276 mm |
| Package weight | 540 g |
| Package depth | 180 mm |

| Operational conditions | |
|---|---|
| Operating relative humidity (H-H) | 20 - 80% |
| Operating temperature (T-T) | 0 - 40 °C |
| Storage temperature (T-T) | -20 - 60 °C |

| Other features | |
|---|---|
| Recyclable packaging material | 100% |
| Compliance certificates | RoHS |

| Technical details | |
|---|---|
| Lifetime | 3 years |

| Logistics data | |
|---|---|
| Harmonized System (HS) code | 85285210 |

8712581764838

**Catalog Object Cloud**

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date