

Epson SureColor SC-P700 photo printer Inkjet 5760 x 1440 DPI 13" x 19" (33x48 cm) Wi-Fi



Brand : Epson

Product family: SureColor

Product code: C11CH38401DA

Product name : SC-P700

- Quality output: Black enhance overcoat technology for finer detail and texture
- Design: Refreshingly understated product design
- Highly-intuitive: 4.3-inch LCD optical touchscreen
- Flexible: Easily handles different media types
- Compact: Smallest footprint and lightest in its class

4.3" LCD touchscreen, Epson Micro Piezo, 5760 x 1440 DPI, USB 3.0, LAN IEEE 802.11, WLAN

2.4GH/5GHz, Wi-Fi Direct, Manual duplex, 39 dB, 12.6 kg

Epson SureColor SC-P700. Print technology: Inkjet, Maximum resolution: 5760 x 1440 DPI. Maximum print size: 13" x 19" (33x48 cm). Borderless printing, Duplex printing. Wi-Fi. Product colour: Black



Printing		Network	
Borderless printing *	✓	Ethernet LAN *	✓
Duplex printing	✓	Bluetooth *	✗
Duplex printing mode	Manual	Mobile printing technologies	Apple AirPrint, Epson Connect, Google Cloud Print
Print technology *	Inkjet		
Maximum resolution *	5760 x 1440 DPI		
Features		Performance	
Market positioning *	Professional	Sound pressure level (printing)	39 dB
Product colour *	Black	Power	
Number of print cartridges	10	Power source *	AC
	Cyan, Grey, Light Cyan, Light grey, Matte black, Photo black, Violet, Vivid light magenta, Vivid magenta, Yellow	Power consumption (printing) *	22 W
Printing colours		Power consumption (standby)	1.1 W
Built-in display	✓	Power consumption (off)	0.18 W
Display	LCD	AC input voltage	100 - 240 V
Display diagonal	10.9 cm (4.3")	AC input frequency	50 - 60 Hz
Control type	Touch	System requirements	
Input & output capacity		Windows operating systems supported	Windows 10, Windows 7, Windows 8, Windows 8.1
Total input capacity	120 sheets	Mac operating systems supported	Mac OS X 10.6 Snow Leopard
Paper handling		Weight & dimensions	
Maximum print size *	13" x 19" (33x48 cm)	Width	515 mm
Maximum ISO A-series paper size	A3+	Depth	368 mm
ISO A-series sizes (A0...A9)	A3, A3+, A4, A5	Height	185 mm
Printing sizes	9 x 12, 10 x 15, 13 x 18, 13 x 20, 20 x 25	Weight	12.6 kg
Ports & interfaces		Packaging data	
Direct printing *	✗	Package width	485 mm
PictBridge *	✗	Package depth	650 mm
USB port *	✓	Package height	340 mm
USB connector	USB Type-A	Package weight	17.2 kg
Network		Logistics data	
Wi-Fi *	✓	Harmonized System (HS) code	84433210



8715946686585

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.