

Epson EB-982W Standard throw projector 4200 ANSI lumens 3LCD WXGA (1280x800) White



Brand : Epson

Product code: V11H987040

Product name : EB-982W

- 4,200lm and 16,000:1 contrast ratio vivid display: 3LCD technology and equally high White and Colour Light Output

- Minimal maintenance: Years of uninterrupted use before maintenance is required
- Flexible installation: Horizontal/vertical keystone correction and 1.6x optical zoom
- Enhanced connectivity: Dual HDMI ports, RJ-45 Ethernet, optional wireless connectivity
- Collaborative features: iProjection App1, split-screen function, moderator function

3LCD, 4200 lm, WXGA, 1280 x 800, 16:10, 16,000 : 1

Epson EB-982W. Projector brightness: 4200 ANSI lumens, Projection technology: 3LCD, Projector native resolution: WXGA (1280x800). Light source type: Lamp, Service life of light source: 6500 h, Service life of light source (economic mode): 17000 h. Focal length range: 18.2 - 29.2 mm, Aperture range (F-F): 1.51 - 1.99, Zoom type: Manual. Video processing: 10 bit, Video colour modes: Blackboard, Cinema, Dynamic, Sports, sRGB. Serial interface type: RS-232C

Projector		Multimedia	
Screen size compatibility *	584.2 - 7112 mm (23 - 280")	Built-in speaker(s) *	✓
Projection distance (wide)	0.9 - 8.5 m	RMS rated power	16 W
Projection distance (tele)	1.4 - 13.7 m	Design	
Projector brightness *	4200 ANSI lumens	Market positioning *	Portable
Projection technology *	3LCD	Product type *	Standard throw projector
Projector native resolution *	WXGA (1280x800)	Product colour *	White
Contrast ratio (typical) *	16000:1	Placement	Ceiling, Desktop
Native aspect ratio *	16:10	Cable lock slot	✓
Number of colours	1.07 billion colours	Cable lock slot type	Kensington
Projector brightness (economic mode)	2600 ANSI lumens	Power	
Vertical scan range	100 - 120 Hz	Power source *	AC
Keystone correction, horizontal	-30 - 30°	Power consumption (typical) *	327 W
Keystone correction, vertical	-30 - 30°	Power consumption (standby) *	0.3 W
Matrix size	1.5 cm (0.59")	Power consumption (economy mode)	225 W
Light source		AC input voltage	100-240 V
Light source type *	Lamp	AC input frequency	50 - 60 Hz
Service life of light source *	6500 h	Software	
Service life of light source (economic mode)	17000 h	Software support	via: AMX, Crestron (Network), Control4, Extron
Lamp type	UHE	Operational conditions	
Lamp power	230 W	Operating temperature (T-T)	5 - 35 °C
Lens system		Storage temperature (T-T)	-10 - 60 °C
Focal length range	18.2 - 29.2 mm	Operating relative humidity (H-H)	20 - 80%
Aperture range (F-F)	1.51 - 1.99	Storage relative humidity (H-H)	10 - 90%
Zoom capability	✓	Weight & dimensions	
Zoom type	Manual	Width	309 mm
Zoom ratio	1.6:1	Depth	282 mm
Throw ratio	1.38 - 2.24:1	Height	90 mm
Video		Weight *	3.1 kg
Full HD *	✗	Package width	385 mm
3D *	✗	Package depth	395 mm
Video processing	10 bit	Package height	175 mm
Video colour modes	Blackboard, Cinema, Dynamic, Sports, sRGB	Package weight	4.68 kg

Ports & interfaces		Packaging content	
USB 2.0 ports quantity	1	Remote control included *	✓
USB 2.0 Type-B ports quantity	1	Batteries included	✓
Serial interface type *	RS-232C	Cables included	AC, HDMI
VGA (D-Sub) ports quantity *	2	Quick start guide	✓
HDMI ports quantity *	2	WLAN adapter included	✓
Composite video in *	1	Bundled software	EasyMP Multi PC Projection, Epson Projektor Management
DVI port *	✗		
Network		Technical details	
Ethernet LAN *	✓	USB display function	3 in 1: Image / Mouse / Sound
Ethernet LAN (RJ-45) ports	1		
Features		Logistics data	
Noise level (economic mode)	28 dB	Quantity per pack	1 pc(s)
Noise level *	37 dB	Products per pallet	72 pc(s)
Country of origin	Philippines	Pallet gross weight	0 g
Password protection	✓	Products per pallet (UK)	72 pc(s)
		Pallet weight (UK)	0 g
		Harmonized System (HS) code	85286200
		Other features	
		Supported network protocols	PJLink



8715946680774

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.