



BenQ LU935 Standard throw projector 6000 ANSI lumens DLP WUXGA (1920x1200) White

Brand : BenQ

Product code: 9H.JNN77.15E

Product name : LU935



- Large H/V lens shift and 1.6X Big zoom perfect for in-house installation
- Native resolution switch to 1080P for multi-display compatibility
- HDMI 2.0 ports with less friction and great brightness
- IP5X dustproof mechanism reducing maintenance costs

DLP, 1920x1200, 6000 lm, HDMI, VGA, LAN, RS-232, USB, 100-240V, 416x166x351 mm

BenQ LU935. Projector brightness: 6000 ANSI lumens, Projection technology: DLP, Projector native resolution: WUXGA (1920x1200). Light source type: Laser, Service life of light source: 20000 h. Focus: Manual, Aperture range (F-F): 1.83 - 1.86, Zoom ratio: 1.6:1. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 480 (VGA), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size

Projector		Ports & interfaces	
Screen size compatibility *	762 - 7620 mm (30 - 300")	DVI port *	✗
Contrast ratio (dynamic)	3000000:1	AC (power) in	✓
Projector brightness *	6000 ANSI lumens	Network	
Projection technology *	DLP	Smart TV *	✗
Projector native resolution *	WUXGA (1920x1200)	Ethernet LAN *	✓
Contrast ratio (typical) *	3000000:1	Ethernet LAN (RJ-45) ports	1
Native aspect ratio *	16:10	Wi-Fi *	✗
Number of colours	1.07 billion colours	Storage	
Horizontal scan range	15 - 102 kHz	Card reader integrated *	✗
Vertical scan range	24 - 120 Hz	Features	
Keystone correction, horizontal	-30 - 30°	Interactive *	✗
Keystone correction, vertical	-30 - 30°	HDCP	✓
Matrix size	1.22 cm (0.48")	On Screen Display (OSD)	✓
Light source		Multimedia	
Light source type *	Laser	Built-in speaker(s) *	✓
Service life of light source *	20000 h	RMS rated power	10 W
Lens system		Design	
Focus *	Manual	Market positioning *	Business
Aperture range (F-F)	1.83 - 1.86	Product type *	Standard throw projector
Zoom capability	✓	Product colour *	White
Zoom ratio	1.6:1	Cable lock slot	✓
Throw ratio	1.36 - 2.18	Cable lock slot type	Kensington
Horizontal lens shift range	-23 - 23%	Display	
Vertical lens shift range	-60 - 60%	Built-in display *	✗
Video			
Analog signal format system *	NTSC, PAL, SECAM		
Full HD *	✓		

Video		Power	
Supported graphics resolutions	640 x 480 (VGA)	Power source *	AC
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p	Power consumption (typical) *	440 W
Ports & interfaces		Power consumption (standby) *	0.5 W
HDMI connector type	Full-size	AC input voltage	100 - 240 V
HDBaseT port	✓	AC input frequency	50 - 60 Hz
USB 2.0 ports quantity	1	Operational conditions	
Serial interface type *	RS-232	Operating temperature (T-T)	0 - 40 °C
PC Audio in	✓	Weight & dimensions	
PC Audio out	✓	Width	416 mm
VGA (D-Sub) ports quantity *	2	Depth	351 mm
HDMI ports quantity *	2	Height	166 mm
		Weight *	7 kg
		Packaging content	
		Remote control included *	✓
		Cables included	AC
		Logistics data	
		Harmonized System (HS) code	85286200



4718755084591

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.