



AOC 27E3UM computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD Black

Brand : AOC

Product code: 27E3UM/BK

Product name : 27E3UM

- 4 ms response time GtG
- VA
- 27"
- FHD (1920x1080 px)
- Low blue light
- Flicker-Free

Screen size (inch) 27, Panel resolution 1920x1080, Refresh rate 75 Hz, Panel type VA, HDMI HDMI 1.4 x 1, Display Port DisplayPort 1.2 x 1, D-SUB (VGA) 1x, DVI 0x, Sync technology (VRR) Adaptive Sync

[AOC 27E3UM computer monitor 68.6 cm \(27"\) 1920 x 1080 pixels Full HD Black:](#)

27" FHD VA display with essential features to get the most out of long working hours

The AOC 27E3UM offers all essentials for working or studying. This model mixes a great 27" VA panel with wide viewing angle and FHD resolution, features for eye care such as Low Blue Mode and Flicker Free and built-in speakers to easily enjoy quality audio. For a neat workstation, this model also offers cable management.



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	Audio input	✓
Display resolution *	1920 x 1080 pixels	Headphone out *	✓
HD type *	Full HD	Headphone connectivity	3.5 mm
Native aspect ratio *	16:9	Built-in KVM switch	✗
Panel type *	VA	HDCP	✓
LED backlight	✓	HDCP version	1.4
Backlight type	W-LED	Mobile High-Definition Link (MHL)	✗
Touchscreen *	✗		
Display brightness (typical)	300 cd/m²	Network	
Response time *	4 ms	Ethernet LAN	✗
Response time measurement type	GTG (Gray to Gray)	Ergonomics	
Anti-glare screen	✓	VESA mounting *	✓
Screen shape *	Flat	Panel mounting interface	100 x 100 mm
Contrast ratio (typical) *	3000:1	Cable lock slot *	✓
Contrast ratio (dynamic)	20000000:1	Cable lock slot type	Kensington
Maximum refresh rate *	75 Hz	Height adjustment *	✗
Viewing angle, horizontal	178°	Pivot	✗
Viewing angle, vertical	178°	Tilt adjustment	✓
Display number of colours *	16.7 million colours	Tilt angle range	5 - 23°
Pixel pitch	0.3114 x 0.3114 mm	On Screen Display (OSD)	✓
Pixel density	82 ppi	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish
Display diagonal (metric)	68.6 cm		
Surface hardness	3H		
sRGB coverage (typical)	115%		
NTSC coverage (typical)	100%		
Adobe RGB coverage	98%		
Performance		Power	
NVIDIA G-SYNC *	✗	Energy efficiency class (SDR) *	E

Performance		Power	
AMD FreeSync *	✗	Power consumption (typical) *	16.27 W
Fast charging	✓	Power consumption (standby) *	0.5 W
Flicker-free technology	✓	Power consumption (off)	0.3 W
Low Blue Light technology	✓	AC input voltage	100 - 240 V
Multimedia		AC input frequency	50/60 Hz
Number of speakers	2	Power supply type	Internal
RMS rated power	4 W	Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	614.7 mm
Built-in camera *	✗	Depth (with stand)	201.3 mm
Design		Height (with stand)	449.1 mm
Market positioning *	Home	Weight (with stand)	4.34 kg
Product colour *	Black	Width (without stand)	614.7 mm
Front bezel colour	Black	Depth (without stand)	52.8 mm
Detachable stand	✓	Height (without stand)	369.6 mm
Ports & interfaces		Packaging data	
Built-in USB hub *	✓	Package width	691 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package depth	142 mm
USB Type-A downstream ports quantity	2	Package height	452 mm
VGA (D-Sub) ports quantity	1	Package weight	6.39 kg
DVI port	✗	Packaging content	
HDMI *	✓	Stand included	✓
HDMI ports quantity	1	Cables included	AC, HDMI
HDMI version	1.4	HDMI cable length	1.8 m
DisplayPorts quantity	1	Power cable length	1.8 m
DisplayPort version	1.2	Other features	
		Exterior finish type	Textured
		Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Light effects	✗
		Supplied AC adapter type	False



4038986180696

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.