

Epson CO-FH02 3000 ANSI lumens 3LCD 1080p (1920x1080) White

Brand : Epson

Product code: V11HA85040

Product name : CO-FH02



3LCD Technology, 0.62", UHE, 188 W, 26" - 391", 2.6 kg

Epson CO-FH02 3000 ANSI lumens 3LCD 1080p (1920x1080) White:

Smart Full HD projector

Project a big screen experience in the home or office. This affordable solution is easy-to-use, Full HD and also has Android TV3.

Creating the big screen experience at home is easy when you've got this Full HD projector, it's ideal for the office or classroom too. You can achieve an impressive 391 inch display and has Android TV3. It's simple to set up and includes 3,000 lumens of brightness for a clear and bright image. A long-lasting solution with the lamp life providing 18 years' worth of entertainment¹.

Projector		Storage	
Smart projector *	✓	Card reader integrated *	✗
Screen size compatibility *	660.4 - 9931.4 mm (26 - 391")	Features	
Projection distance	0.9 - 10.4 m	Noise level (economic mode)	29 dB
Projector brightness *	3000 ANSI lumens	Noise level *	37 dB
Projection technology *	3LCD	Country of origin	Philippines
Projector native resolution *	1080p (1920x1080)	Multimedia	
Native aspect ratio *	16:9	Built-in speaker(s) *	✓
Number of colours	16.7 million colours	RMS rated power	5 W
Keystone correction, horizontal	-30 - 30°	Design	
Keystone correction, vertical	-30 - 30°	Market positioning *	Home cinema
Matrix size	1.57 cm (0.62")	Product colour *	White
Light source		Placement	Desktop
Light source type *	Lamp	Cable lock slot	✓
Service life of light source *	6000 h	Cable lock slot type	Kensington
Service life of light source (economic mode)	12000 h	Display	
Lamp type	UHE	Built-in display *	✗
Lamp power	188 W	Power	
Lens system		Power source *	AC
Focus *	Manual	Power consumption (typical) *	270 W
Fixed focal length	1.44 mm	Power consumption (standby) *	0.5 W
Aperture range (F-F)	1 - 1.35	Power consumption (economy mode)	214 W
Zoom capability	✓	Operational conditions	
Throw ratio	1.19 - 1.61:1	Operating temperature (T-T)	5 - 40 °C
Video		Storage temperature (T-T)	-10 - 60 °C
Analog signal format system *	Not supported	Weight & dimensions	
Full HD *	✓	Width	320 mm
3D *	✗	Depth	211 mm
Supported video modes	1080p	Height	87 mm
Ports & interfaces		Weight *	2.6 kg
HDMI version	1.4	Package width	328 mm
USB 2.0 ports quantity	2	Package depth	385 mm
USB 2.0 Type-A ports quantity	1	Package height	165 mm
HDMI ports quantity *	1	Package weight	4.01 kg
Network		Packaging content	
Smart TV *	✓	Remote control included *	✓

Packaging content	
Batteries included	✓
Cables included	AC
Logistics data	
Harmonized System (HS) code	85286200000



8715946706832

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.