



AOC V5 27V5CE/BK computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black

Brand : AOC

Product family: V5

Product code: 27V5CE/BK

Product name : 27V5CE/BK

Screen size (inch) 27, Panel resolution 1920x1080, Refresh rate 75 Hz, Response time MPRT 1 ms, Panel type IPS, USB-C connectivity USB-C 3.2 x 1 (DP alt mode, upstream, power delivery up to 65 W), HDMI HDMI 1.4 x 1, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Freesync

AOC V5 27V5CE/BK computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black:

27" IPS FHD panel for boosting productivity at home, with USB-C and PD65W

The AOC 27V5CE is a three-side frameless monitor powered by a 27" IPS panel with FHD resolution for a great viewing experience, ready to boost your productivity with USB-C with Power Delivery up to 65W, 4 USB ports & HDMI.

AOC V5 27V5CE/BK. Display diagonal: 68.6 cm (27"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDMI *	✓
Display resolution *	1920 x 1080 pixels	HDMI ports quantity	1
HD type *	Full HD	HDMI version	1.4
Native aspect ratio *	16:9	Headphone out *	✓
Display technology *	LED	Headphone outputs	1
Panel type *	IPS	Headphone connectivity	3.5 mm
LED backlight	✓	Built-in KVM switch	✗
Backlight type	W-LED	HDCP	✓
Touchscreen *	✗	HDCP version	1.4
Display brightness (typical)	300 cd/m²	Charging port type	USB Type-C
Response time *	4 ms	AC (power) in	✓
Response time measurement type	GTG (Gray to Gray)	Mobile High-Definition Link (MHL)	✗
Response time (MPRT)	1 ms		
Anti-glare screen	✓	Network	
Screen shape *	Flat	Ethernet LAN	✗
Contrast ratio (typical) *	1000:1	Ergonomics	
Contrast ratio (dynamic)	20000000:1	VESA mounting *	✓
Maximum refresh rate *	75 Hz	Panel mounting interface	100 x 100 mm
Viewing angle, horizontal	178°	Wall mountable	✓
Viewing angle, vertical	178°	Cable lock slot *	✓
Display number of colours *	16.7 million colours	Cable lock slot type	Kensington
Pixel pitch	0.3114 x 0.3114 mm	Pivot	✗
Pixel density	82 ppi	Tilt adjustment	✓
Display diagonal (metric)	68.6 cm	Tilt angle range	3 - 21°
Surface hardness	6H	LED indicators	✓
sRGB coverage (typical)	122%		
NTSC coverage (typical)	106%	Power	
Adobe RGB coverage	104%	Energy efficiency class (SDR) *	E
DCI-P3 coverage	97%		

Performance		Power	
AMD FreeSync *	✓	Power consumption (typical) *	30 W
AMD FreeSync type	FreeSync	Power consumption (standby) *	0.5 W
Fast charging	✓	Power consumption (off)	0.3 W
Flicker-free technology	✓	AC input voltage	100 - 240 V
Low Blue Light technology	✓	AC input frequency	50 - 60 Hz
		Power supply type	Internal
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	450.4 mm
RMS rated power	6 W	Depth (with stand)	185 mm
Built-in speaker(s) *	✓	Height (with stand)	613 mm
Built-in microphone	✗	Weight (with stand)	5.53 kg
Built-in camera *	✗	Width (without stand)	363.4 mm
		Depth (without stand)	43.9 mm
		Height (without stand)	613 mm
Design		Packaging data	
Market positioning *	Home	Package width	840 mm
Product colour *	Black	Package depth	141 mm
Frameless design	✓	Package height	456 mm
Front bezel colour	Black	Package weight	8.45 kg
Detachable stand	✓	USB cable length	1.8 m
Feet colour	Black		
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	AC, HDMI, USB Type-C
USB upstream port type	USB Type-C	HDMI cable length	1.5 m
Number of upstream ports	1		
USB Type-A downstream ports quantity	4		
USB Type-C DisplayPort Alternate Mode	✓		
USB Power Delivery (USB PD)	✓		
USB Power Delivery up to	65 W		
DVI port	✗		
		Other features	
		Exterior finish type	Matt
		Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Compliance certificates	CE
		Mean time between failures (MTBF)	50000 h
		Light effects	✗
		Certification	CB,EAC



4038986180146

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.