



APC SRV6KI uninterruptible power supply (UPS) Double-conversion (Online) 6 kVA 6000 W

Brand : APC

Product code: SRV6KI

Product name : SRV6KI

SRV 6000VA, 230 Vac, 50 Hz / 60 Hz, 6000 VA / 6000 W, 220 Vac, 240 Vac, 94% max, 192 V
APC SRV6KI. UPS topology: Double-conversion (Online), Output power capacity: 6 kVA, Output power: 6000 W. AC outlet types: Hard Wire 3-wire (1P + N + E), Serial interface type: RS-232. Battery capacity: 7 Ah, Battery capacity: 192 VAh, Battery voltage: 12 V. Form factor: Tower, Product colour: Black, Display type: LCD. Cables included: Input power cable, Output power cable, RS-232, USB cable



Features		Design	
UPS topology *	Double-conversion (Online)	Form factor *	Tower
Output power capacity *	6 kVA	Product colour *	Black
Output power *	6000 W	Display type	LCD
Input operation voltage (min) *	110 V	Operational conditions	
Input operation voltage (max) *	300 V	Operating temperature (T-T)	0 - 40 °C
Input frequency *	50/60 Hz	Storage temperature (T-T)	-15 - 60 °C
Output operation voltage (min)	220 V	Operating relative humidity (H-H)	0 - 95%
Output operation voltage (max)	240 V	Storage relative humidity (H-H)	0 - 95%
Surge energy rating	600 J	Operating altitude	0 - 3000 m
Efficiency	94%	Non-operating altitude	0 - 15000 m
Crest factor	3:1	Packaging content	
Emergency Power Off (EPO)	✓	Cables included	Input power cable, Output power cable, RS-232, USB cable
Socket circuit breaker	✓	Management card included	✗
Ports & interfaces		Manual	✓
AC outlet types	Hard Wire 3-wire (1P + N + E)	Weight & dimensions	
USB port	✓	Width	190 mm
USB 2.0 ports quantity	1	Depth	374 mm
Serial interface	✓	Height	685 mm
Serial interface type	RS-232	Weight	5.4 kg
RS-232 ports	1	Packaging data	
SmartSlot	✓	Warranty card	✓
SmartConnect port	✗		

Battery		Packaging data	
Battery capacity	7 Ah	Software CD	✓
Battery capacity	192 VAh	Package width	291 mm
Battery voltage	12 V	Package depth	495 mm
		Package height	910 mm
		Package weight	66 kg
Logistics data			
		Harmonized System (HS) code	85078000



0731304338017



731304338017

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.