



AOC V5 Q27V5N/BK computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LED Black

Brand : AOC

Product family: V5

Product code: Q27V5N/BK

Product name : Q27V5N/BK



Screen size (inch) 27, Panel resolution 2560x1440, Refresh rate 75 Hz, Panel type VA, HDMI HDMI 1.4 x 2, Display Port DisplayPort 1.2 x 2, D-SUB (VGA) 0x, DVI 0x, Sync technology (VRR) Adaptive sync (Freesync Premium Pro after AMD certified)

AOC V5 Q27V5N/BK computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LED Black:

27" VA QHD panel for productivity, comfort, and exceptional viewing experience

The AOC Q27V5N is a three-side frameless monitor equipped with a 27" VA panel with QHD resolution for an amazing viewing experience. This model is ready to boost your productivity with its flexible connectivity (DP and HDMI), while ensuring great comfort with its adjustable stand that easily allows pivot, tilt, and swivel.

AOC V5 Q27V5N/BK. Display diagonal: 68.6 cm (27"), Display resolution: 2560 x 1440 pixels, HD type: Quad HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Height adjustment. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	Mobile High-Definition Link (MHL)	✗
Display resolution *	2560 x 1440 pixels	Network	
HD type *	Quad HD	Ethernet LAN	✗
Native aspect ratio *	16:9	Ergonomics	
Display technology *	LED	Cable lock slot *	✓
Panel type *	VA	Cable lock slot type	Kensington
LED backlight	✓	Height adjustment *	✓
Backlight type	W-LED	Adjustable height (max)	13 cm
Touchscreen *	✗	Pivot	✓
Display brightness (typical)	300 cd/m²	Swivelling	✓
Response time *	4 ms	Tilt adjustment	✓
Response time measurement type	GTG (Gray to Gray)	Tilt angle range	3.5 - 21.5°
Anti-glare screen	✓	On Screen Display (OSD)	✓
Screen shape *	Flat	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
Contrast ratio (typical) *	4000:1		
Contrast ratio (dynamic)	20000000:1	Number of OSD languages	19
Maximum refresh rate *	75 Hz	LED indicators	✓
Viewing angle, horizontal	178°	Power	
Viewing angle, vertical	178°	Energy efficiency class (SDR) *	F
Display number of colours *	16.7 million colours	Energy efficiency class (HDR) *	F
Pixel pitch	0.2331 x 0.2331 mm	Energy consumption (SDR) per 1000 hours *	25 kWh
Pixel density	108.8 ppi	Energy consumption (HDR) per 1000 hours *	25 kWh
Display diagonal (metric)	68.6 cm		
Surface hardness	6H		
sRGB coverage (typical)	110%		
NTSC coverage (typical)	94%		
Adobe RGB coverage	95%		
DCI-P3 coverage	88%		

Performance		Power	
NVIDIA G-SYNC *	✗	Power consumption (typical) *	30 W
AMD FreeSync *	✓	Power consumption (standby) *	0.5 W
AMD FreeSync type	FreeSync Premium Pro	Power consumption (off)	0.3 W
Fast charging	✗	AC input voltage	100 - 240 V
Flicker-free technology	✓	AC input frequency	50/60 Hz
Low Blue Light technology	✓	Power supply type	Internal
		Energy efficiency scale	A to G
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	613 mm
RMS rated power	6 W	Depth (with stand)	200 mm
Built-in speaker(s) *	✓	Height (with stand)	516.6 mm
Built-in microphone	✗	Weight (with stand)	6.08 kg
Built-in camera *	✗	Width (without stand)	613 mm
		Depth (without stand)	44.6 mm
		Height (without stand)	363.4 mm
Design		Packaging data	
Market positioning *	Home	Package width	840 mm
Product colour *	Black	Package depth	141 mm
Frameless design	✓	Package height	456 mm
Front bezel colour	Black	Package weight	8.53 kg
Detachable stand	✓		
Feet colour	Black		
Ports & interfaces		Packaging content	
Built-in USB hub *	✗	Stand included	✓
DVI port	✗	Cables included	AC, HDMI
HDMI *	✓	HDMI cable length	1.5 m
HDMI ports quantity	2		
HDMI version	1.4		
DisplayPorts quantity	2		
DisplayPort version	1.2		
Headphone out *	✓		
Headphone outputs	1		
Headphone connectivity	3.5 mm		
Built-in KVM switch	✗		
HDCP	✓		
HDCP version	1.4		
AC (power) in	✓		
		Sustainability	
		Doesn't contain	Mercury, PVC/BFR
		Other features	
		Exterior finish type	Matt
		Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Compliance certificates	CE
		Mean time between failures (MTBF)	50000 h
		Light effects	✗
		Supplied AC adapter type	False
		Certification	WEEE,REACH compliant,RoHs compliant,CB,TUV-Bauart-Mark,ISO 9241-307,EAC



4038986180412

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.