



AOC AGON 5 AG275QZN/EU computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD Black, Red

Brand : AOC

Product family: AGON 5

Product code: AG275QZN/EU

Product name : AG275QZN/EU

- SCREEN SIZE (INCH) 27
- PANEL RESOLUTION 2560x1440
- PANEL TYPE VA
- SYNC TECHNOLOGY (VRR)
- Freesync Premium
- REFRESH RATE 240Hz
- RESPONSE TIME GTG 1 ms
- RESPONSE TIME MPRT 0.5 ms
- HDR (HIGH DYNAMIC RANGE)
- Vesa Certified DisplayHDR 400

Screen size (inch) 27, Panel resolution 2560x1440, Refresh rate 240 Hz, Response time MPRT 0.5 ms, Panel type VA, HDMI HDMI 2.0 x 2, Display Port DisplayPort 1.4 x 2, Sync technology (VRR) Adaptive Sync



AOC AGON 5 AG275QZN/EU computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD Black, Red:

27" QHD VA display with astounding 240Hz refresh rate and super-fast 0,5 ms MPRT

The AG275QZN offers the best gaming experience with its fast VA panel with excellent QHD resolution and great contrast, the astounding 240Hz refresh rate and super-fast 0,5 ms MPRT. Compatible with next gen consoles, always get the upper hand.

Display		Network	
Display diagonal *	68.6 cm (27")	Wi-Fi	✗
Display resolution *	2560 x 1440 pixels	Bluetooth	✗
HD type *	Quad HD	Ethernet LAN	✗
Native aspect ratio *	16:9	Ergonomics	
Panel type *	VA	VESA mounting *	✓
LED backlight	✓	Panel mounting interface	100 x 100 mm
Backlight type	W-LED	Cable lock slot *	✓
Touchscreen *	✗	Cable lock slot type	Kensington
Display brightness (typical)	400 cd/m²	Height adjustment *	✓
Response time *	1 ms	Adjustable height (max)	15 cm
Response time measurement type	GTG (Gray to Gray)	Pivot	✓
Response time (MPRT)	0.5 ms	Swivelling	✓
Anti-glare screen	✓	Swivel angle range	-20 - 20°
Screen shape *	Flat	Tilt adjustment	✓
Supported video modes	1080p, 1440p, 2160p	Tilt angle range	-5 - 23°
Contrast ratio (typical) *	3000:1	On Screen Display (OSD)	✓
Contrast ratio (dynamic)	80000000:1	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
Maximum refresh rate *	240 Hz		
Viewing angle, horizontal	178°	Number of OSD languages	19
Viewing angle, vertical	178°	Plug and Play	✓
Display number of colours *	16.7 million colours	Power	
Pixel density	109 ppi	Energy efficiency class (SDR) *	F
Digital horizontal frequency	30 - 255 kHz	Energy efficiency class (HDR) *	G
Digital vertical frequency	48 - 240 Hz		
Display diagonal (metric)	68.6 cm		
High Dynamic Range (HDR) supported	✓		
High Dynamic Range (HDR) technology	DisplayHDR 400		

Display		Power	
Colour gamut standard	DCI-P3	Energy consumption (SDR) per 1000 hours *	26 kWh
Colour gamut	90%	Energy consumption (HDR) per 1000 hours *	60 kWh
sRGB coverage (typical)	100%	Power consumption (typical) *	23 W
Adobe RGB coverage	100%	Power consumption (standby) *	0.5 W
DCI-P3 coverage	90%	Power consumption (off)	0.3 W
Performance		Power supply type	Internal
AMD FreeSync *	✓	Energy efficiency scale	A to G
AMD FreeSync type	FreeSync Premium	Weight & dimensions	
Fast charging	✓	Width (with stand)	613.4 mm
VESA Adaptive Sync support	✓	Depth (with stand)	231.8 mm
Flicker-free technology	✓	Height (with stand)	561.1 mm
Low Blue Light technology	✓	Weight (with stand)	5.92 kg
Game mode	✓	Width (without stand)	613.4 mm
Multimedia		Depth (without stand)	50.3 mm
Built-in speaker(s) *	✗	Height (without stand)	365.7 mm
Built-in camera *	✗	Weight (without stand)	5.92 kg
Design		Packaging data	
Market positioning *	Gaming	Package width	780 mm
Product colour *	Black, Red	Package depth	478 mm
Frameless design	✓	Package height	189 mm
Front bezel colour	Black/Red	Package weight	9.38 kg
Detachable stand	✓	Package type	Box
Feet colour	Black	USB cable length	1.8 m
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Cables included	AC, HDMI, USB
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Power adapter included	✓
USB Type-A downstream ports quantity	4	HDMI cable length	1.8 m
HDMI *	✓	Other features	
HDMI ports quantity	2	Brand specific technologies	Crosshair
HDMI version	2.0	Low input lag	✓
DisplayPorts quantity	2	FPS counter	✓
DisplayPort version	1.4	Dial point	✓
Headphone out *	✓	Shadow control	✓
Headphone connectivity	3.5 mm	Motion blur reduction	✓
HDCP	✓	Exterior finish type	Matt
HDCP version	2.2	Bezel thickness type	Frameless
		Warranty period	3 year(s)
		Compliance certificates	CE
		Light effects	✗
		Certification	REACH compliant,RoHs compliant,CB,TUV-Bauart-Mark,ISO 9241-307,EAC,FCC,Microsoft WHQL



4038986180436

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.