



Canon PIXMA G1530 Colour Refillable MegaTank Printer

Brand : Canon

Product family: PIXMA

Product code: 5809C008

Product name : G1530 Colour
Refillable MegaTank Printer

- Refillable home inkjet printer
- A4 print only

- 100-sheet capacity, USB connectivity

A4, 4800 x 1200 dpi, USB Hi-Speed (Typ B), 100-240 V, 50-60 Hz

Canon PIXMA G1530 Colour Refillable MegaTank Printer. Colour, Number of print cartridges: 4. Maximum resolution: 4800 x 1200 DPI. Maximum ISO A-series paper size: A4. Print speed (black, normal quality, A4/US Letter): 11 ppm. Duplex printing. Product colour: Black



Features		Power	
Separate cartridges	✓	Energy Star Typical Electricity Consumption (TEC)	0.1 kWh/week
Duplex printing *	✓	AC input voltage	100 - 240 V
Duplex printing mode	Manual	System requirements	
Printing colours *	Black, Cyan, Magenta, Yellow	Windows operating systems supported	Windows 10, Windows 11, Windows 8.1
Ink tank system	✓	Mac operating systems supported	Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina, Mac OS X 10.2 Jaguar, Mac OS X 10.3 Panther, Mac OS X 10.4 Tiger, Mac OS X 10.5 Leopard, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks, Mac OS X 11.0 Big Sur, Mac OS X 12.0 Monterey
Colour *	✓		Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019, Windows Server 2022
Number of print cartridges *	4	Server operating systems supported	Windows Server 2012 R2, Windows Server 2016, Windows Server 2019, Windows Server 2022
Printing		Other operating systems supported	ChromeOS
Print speed (colour, draft quality, A4/US Letter)	6 ppm	Operational conditions	
Maximum resolution *	4800 x 1200 DPI	Operating temperature (T-T)	5 - 35 °C
Print speed (black, normal quality, A4/US Letter) *	11 ppm	Operating relative humidity (H-H)	10 - 90%
Borderless printing	✓	Weight & dimensions	
Input & output capacity		Width	416 mm
Total number of input trays *	1	Depth	557 mm
Total input capacity *	100 sheets	Height	267 mm
Paper handling	Maximum print size	Weight	4.6 kg
	Maximum ISO A-series paper size *	Packaging data	
	Paper tray media types *	Cartridge(s) included	✓
	ISO A-series sizes (A0...A9) *		
	ISO B-series sizes (B0...B9)		
	Non-ISO print media sizes		
	Envelopes sizes		
	Photo paper sizes		
	Paper tray media weight		

Ports & interfaces		Packaging data	
USB port *	✓	Included cartridge capacity (black)	6000 pages
Network		Included cartridge capacity (CMY)	7700 pages
Ethernet LAN *	✗	Included cartridge capacity (economy mode, black)	7600 pages
Wi-Fi *	✗	Included cartridge capacity (economy mode, CMY)	8100 pages
Wi-Fi Direct *	✗	Cables included	AC
Design		Bundled software	IJ Printer Assistant Tool
Market positioning *	Home & office	Package width	494 mm
Product colour *	Black	Package depth	499 mm
Built-in display *	✗	Package height	245 mm
Country of origin	Vietnam	Package weight	8.7 kg
Power		Logistics data	
Power consumption (printing) *	14 W	Pallet gross length	100.3 cm
Power consumption (off)	0.1 W	Pallet gross width	99.1 cm
Power consumption (standby)	0.6 W	Pallet gross height	98.5 cm
		Pallet gross weight	140.9 kg
		Products per pallet	16 pc(s)
Other features			
		Warranty period	2 year(s)



4549292205923

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.