APC NetShelter SX, Server Rack Enclosure, 12U, Shock Packaging, Black, 658H x 600W x 900D mm





Brand : APC

Product code: AR3003SP

Product name : NetShelter SX, Server Rack Enclosure, 12U, Shock Packaging, Black, 658H x 600W x 900D mm

- Feature-rich rack enclosure optimized for easy installation, managing cables, integrating power distribution, and maximizing airflow
- Includes: Casters, Comms cable, Doors, Key(s), Leveling feet, Pallet ramps, Reusable packaging, Roof, Side panels
NetShelter SX, Server Rack Enclosure, 12U, Shock Packaging, Black, 658H x 600W x 900D mm

APC NetShelter SX, Server Rack Enclosure, 12U, Shock Packaging, Black, 658H x 600W x 900D mm:

An industry standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices. Shock pallet and shock packaging simplifies IT “rack and stack” for equipment integrators.

Features	
Rack capacity *	12U
Type *	Freestanding rack
Maximum weight capacity *	272 kg
Product colour	Black
Frame type	Closed
Back door construction	Perforated
Removable back door	✔
Removable front door	✔
Removable side panels	✔
Side panels included	✔
Key lock	✔
Side panel key lock	✔
Adjustable mounting rails	✔
Adjustable feet	✔
Cable management	✔
Castor wheels	✔
International Protection (IP) code	IP20

Features	
Certification	UL 2416, UL 60950-1 REACH
Weight & dimensions	
Width	600 mm
Depth	900 mm
Height	658 mm
Weight	54 kg
Mounting depth (min)	19.1 cm
Mounting depth (max)	75.6 cm
Packaging data	
Package width	750 mm
Package depth	1070 mm
Package height	960 mm
Package weight	108 kg
Technical details	
Total carbon footprint (kg of CO2e)	327.7
Compliance certificates	RoHS
Logistics data	
Harmonized System (HS) code	85381000

0731304347644

731304347644

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date