



APC G55TUPSU60HS uninterruptible power supply (UPS) Double-conversion (Online) 60 kVA 54000 W

Brand : APC

Product code: G55TUPSU60HS

Product name : G55TUPSU60HS

60kVA 400V Single UPS, Start-up 5x8, 3-phase

APC G55TUPSU60HS uninterruptible power supply (UPS) Double-conversion (Online) 60 kVA 54000 W:

A versatile 3-phase UPS for facility, industrial and data center applications. Configurable system with a comprehensive range of accessories to meet your application demands.
APC G55TUPSU60HS. UPS topology: Double-conversion (Online), Output power capacity: 60 kVA, Output power: 54000 W. Battery voltage: 432 V, Battery recharge time: 10 h. Product colour: Grey, Display type: LCD, International Protection (IP) code: IP20. Certification: CE, EN/IEC 62040-3, IEC 62040-1-2, IEC 62040-2, ISO 9001, TUV, VDE. Width: 712 mm, Depth: 850 mm, Height: 1900 mm



Features		Design	
UPS topology *	Double-conversion (Online)	International Protection (IP) code	IP20
Output power capacity *	60 kVA	Operational conditions	
Output power *	54000 W	Operating temperature (T-T)	0 - 40 °C
Waveform *	Sine	Storage temperature (T-T)	-20 - 45 °C
Input operation voltage (min) *	250 V	Operating relative humidity (H-H)	0 - 95%
Input operation voltage (max) *	470 V	Storage relative humidity (H-H)	0 - 95%
Input frequency *	45/65 Hz	Operating altitude	0 - 3000 m
Output operation voltage (min)	380 V	Non-operating altitude	0 - 12000 m
Output operation voltage (max)	415 V	Certificates	
Maximum current	88 A	Certification	CE, EN/IEC 62040-3, IEC 62040-1-2, IEC 62040-2, ISO 9001, TUV, VDE
Number of input phases	3	Weight & dimensions	
Efficiency	92.5%	Width	712 mm
Crest factor	3:1	Depth	850 mm
Noise level	55.5 dB	Height	1900 mm
Power protection features	Overload	Weight	400 kg
Battery		Packaging data	
Battery voltage	432 V	Package width	980 mm
Battery recharge time	10 h	Package depth	960 mm
Design		Package height	2030 mm
Product colour *	Grey	Package weight	420 kg
Display type	LCD	Other features	
		Number of phases	3
		Input connection type	Hard Wire 4-wire (3PH + G)
		Nominal output voltage	400 V

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.