



APC BE850G2-IT uninterruptible power supply (UPS) Standby (Offline) 0.85 kVA 520 W

Brand : APC

Product code: BE850G2-IT


Product name : BE850G2-IT

520W, 850VA, 230V, USB Type-C, 47/63 Hz
APC BE850G2-IT. UPS topology: Standby (Offline), Output power capacity: 0.85 kVA, Output power: 520 W. AC outlet types: Type F, USB port type: USB Type-C, Cabling technology: 10/100Base-T. Battery life (max): 5 year(s), Battery recharge time: 16 h. Form factor: Compact, Product colour: Black, Cable length: 1.83 m. Compliance certificates: RoHS, Certification: CE, EAC



Features		Battery	
UPS topology *	Standby (Offline)	Cold start	✓
Output power capacity *	0.85 kVA	Design	
Output power *	520 W	Form factor *	Compact
Waveform *	Sine	Cable length	1.83 m
Input operation voltage (min) *	220 V	Product colour *	Black
Input operation voltage (max) *	230 V	LED indicators	✓
Input frequency *	47/63 Hz	Operational conditions	
Output operation voltage (min)	220 V	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (max)	230 V	Storage temperature (T-T)	-15 - 45 °C
Output frequency	47/63 Hz	Operating relative humidity (H-H)	0 - 90%
Maximum current	6 A	Storage relative humidity (H-H)	0 - 95%
Surge energy rating	310 J	Non-operating altitude	0 - 4500 m
Efficiency	80%	Certificates	
Noise level	45 dB	Compliance certificates	RoHS
Surge protection	✓	Certification	CE, EAC
Surge protection features	Digital Subscriber Line (DSL)	Packaging content	
Audible alarm(s)	✓	Manual	✓
Audible alarm modes	Alarm when on battery, Low battery alarm, Overload alarm	Weight & dimensions	
Ports & interfaces		Width	130 mm
AC outlet types	Type F	Depth	365 mm
USB port	✓	Height	120 mm
USB port type	USB Type-C	Weight	4.5 kg
Ethernet LAN (RJ-45) ports	1	Packaging data	
Cabling technology	10/100Base-T	Package width	186 mm
Battery		Package depth	441 mm
Battery life (max)	5 year(s)	Package height	190 mm
Battery recharge time	16 h		

Battery		Packaging data	
Hot-swap battery	✓	Package weight	5 kg
Automatic battery test	✓	Logistics data	
		Harmonized System (HS) code	85078000
		Master (outer) case gross weight	16 kg



0731304347293



731304347293

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.