

Targus ACH228 Silver

Brand : Targus

Product code: ACH228EU

Product name : ACH228

- Add 2 USB-A 3.2 Gen 1 ports (1 fast charging)* and 2 USB-C ports to your host device
 - Supports up to 5Gbps data transfer rate per USB-A or USB-C port
 - Connect a USB-C device or power adapter to the USB-C port
 - USB-C (3.2 Gen 1 SuperSpeed 5Gbps) port supports power delivery pass-through**
 - USB-C (3.2 Gen 1 SuperSpeed) connector supports power delivery up to 100W upstream*** and Power Delivery 3.0 Fast Role Swap****
 - Thunderbolt™ 3 compatible**
 - Windows®, MacOS® Chrome OS™ compatible
- USB-C Multi-Port Hub, 100W, 2x USB-A, 2x USB-C
- Targus ACH228. Product colour: Silver, Country of origin: China, Compatible products: Thunderbolt 3 host. Compatible operating systems: Windows, MacOS, Chrome OS. Width: 85 mm, Depth: 45 mm, Height: 10 mm. Quantity per pack: 1 pc(s)



Ports & interfaces		Weight & dimensions	
Ports quantity *	4	Width	85 mm
Card reader integrated	✗	Depth	45 mm
DC-in jack	✗	Height	10 mm
Features		Weight	59 g
Product colour	Silver	Packaging data	
Country of origin	China	Quantity per pack	1 pc(s)
Compatible products	Thunderbolt 3 host	Logistics data	
System requirements		Harmonized System (HS) code	84719000
Compatible operating systems	Windows, MacOS, Chrome OS		



5051794030358

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.