

Technical datasheet: FT-35T-2.6A1-475

Specifications:

Resonant Frequency	2.6kHz \pm 0.5kHz
Max Resistance (Zr)	300 Ω
Capacitance	30000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 35mm, d: \varnothing 25mm, T: 0.51mm, t: 0.25mm)

