

Technisches Datenblatt „80 1-stg. Gewebeklebeband“ Technical data sheet „80 one sided Duct Cloth Tape“

Production Specification

Product Name	one sided duct cloth tape
Tape Grade	for packaging & stationery
Article No.	80 Military Cloth Tape
Mesh	80 Mesh
Base Carrier	100% Polyester
Type of adhesive	natural rubber base

<u>TEST ITEM</u>	<u>UNIT</u>	<u>Result</u>
Total thickness	micron	310
Peel adhesion	gf/25mm/180°	1000
Tensile strength	kgf/25mm	16,5
Elongation	%	11,5
Ball tack	Ball No.	18
Holding power	mm/Hr 1 kg loading on SUS plate, 25mmx25mm	0,03
Un-winding force	gf/25 mm	900
Heat resistance	°C	60
Weather resistance	Hrs	8
Average weight	g	
Length	m	50
Delamination	No	

The Statements in this information sheet are based upon our knowledge and practical experience. This data is intended only as a source of information and is given without guarantee and does not constitute a warranty. Suggestion for use and final results on our best technical experiences but cannot be intended as our commitment or liability. The company reserves the right to modify or change the products at any time without notice. All information has to be intended as generic advise for the use of products. Users have to verify the suitability of each tape in actual application under specific conditions.