

Samsung MUF-64BE USB flash drive 64 GB USB Type-A 3.2 Gen 1 (3.1 Gen 1) Silver

Brand : Samsung

Product code: MUF-64BE3/APC

Product name : MUF-64BE

- Transfer files with speeds up to 400MB/s. Performance varies by capacity.
- Reliable and secure storage for your photos, videos, music, and files.
- Durable metal casing with integrated key ring to prevent loss.
- USB 3.2 Gen 1 (Type A) flash drive with backwards compatibility (USB 2.0).
- Protection from water, extreme temperatures, shock, magnets and x-rays.

MUF-64BE3/APC

Samsung MUF-64BE. Capacity: 64 GB, Device interface: USB Type-A, USB version: 3.2 Gen 1 (3.1 Gen 1), Read speed: 300 MB/s, Write speed: 30 MB/s. Form factor: Capless. Password protection. Weight: 10.9 g. Product colour: Silver



Performance		Packaging data	
Capacity *	64 GB	Package width	102 mm
Device interface *	USB Type-A	Package depth	154 mm
USB version *	3.2 Gen 1 (3.1 Gen 1)	Package height	12 mm
Read speed	300 MB/s	Package weight	24 g
Write speed	30 MB/s	Package type	Blister
Plug and Play	✓	Packaging content	
Design		Quantity per pack	1 pc(s)
Form factor *	Capless	Operational conditions	
Product colour *	Silver	Operating temperature (T-T)	-25 - 85 °C
Protection features	Magnet proof, Shock resistant, Temperature proof, Waterproof, X-ray proof	Storage temperature (T-T)	-40 - 85 °C
		Operating shock	1500 G
Waterproof up to	1 m	Operating vibration	15000 G
Certification	KC, FCC, CE, VCCI, RCM	Duration shock	0.5 ms
Security		Other features	
Password protection	✓	Country of origin	Taiwan
Weight & dimensions		Compliance certificates	Federal Communications Commission (FCC), CE, VCCI, RCM
Width	15.5 mm	Compatible products	PC, Notebook
Depth	40 mm	Logistics data	
Height	12 mm	Harmonized System (HS) code	84717070
Weight	10.9 g		



8801643229382



5715063083383

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.