



APC SYMMETRA LX EXTENDED RUN TOWER uninterruptible power supply (UPS) 0.55 kVA 330 W

Brand : APC

Product code: SYAXR9B9I

Product name : SYMMETRA LX EXTENDED RUN TOWER

APC SYMMETRA LX EXTENDED RUN TOWER with W/9 SYBT5, 230V.

APC SYMMETRA LX EXTENDED RUN TOWER uninterruptible power supply (UPS) 0.55 kVA 330 W:

Modular design

- Increases adaptability with an open architecture configurable to any IT environment.
- Modular construction - can be deployed as a non-standby and migrate to a standby (UPS) system.

Hot-swappable batteries

- Ensures clean, uninterrupted power to protected equipment while batteries are being replaced

Battery modules connection in panel

- Delivers higher availability through redundant batteries.

User-replaceable batteries

- Increases availability by allowing a trained user to perform upgrades and replacements of the batteries reducing Mean Time to Repair (MTTR)

Stackable external battery frames

- Saves floor space without compromising runtime requirements.

Plug-and-Play external batteries

- Ensures clean, uninterrupted power to the loads when adding extra runtime to the UPS.



Features		Operational conditions	
Output power capacity *	0.55 kVA	Storage relative humidity (H-H)	0 - 95%
Output power *	330 W	Certificates	
Design		Certification	BSMI/EN 50091-1/EN 50091-2/EN 60950/IEC 60950/VCCI,VDE
Product colour *	Black	Weight & dimensions	
Operational conditions		Weight	349.1 kg
Operating temperature (T-T)	0 - 40 °C	Logistics data	
Storage temperature (T-T)	-15 - 45 °C	Harmonized System (HS) code	85078000
Operating relative humidity (H-H)	0 - 95%	Other features	
		Dimensions (WxDxH)	483 x 726 x 602 mm



0731304233794



731304233794

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.