



Canon PGI-72 MBK/C/M/Y/R 5 Ink Cartridge Multipack

Brand : CanonProduct code: 6402B009

Product name : PGI-72 MBK/C/M/Y/R 5 Ink Cartridge Multipack

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges***
 - Genuine Canon Ink provides consistent quality prints 100% of the time***
 - Genuine Canon Ink is 100% reliable so you can print with less stress***
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-72 MBK/C/M/Y/R 5 Ink Cartridge Multipack



Canon PGI-72 MBK/C/M/Y/R 5 Ink Cartridge Multipack:

This multipack contains one each of matte black, cyan, magenta, yellow and red ink tanks. The set of five colour 14ml ink tanks offer you convenience and savings. The LUCIA system delivers stunning results and longevity. Print up to 1640 10x15 photos or up to 710 10x15 colour photos at ISO/IEC 29102* standard.

Canon PGI-72 MBK/C/M/Y/R 5 Ink Cartridge Multipack. Cartridge capacity: Standard Yield, Supply type: Multi pack, Colour ink page yield: 710 pages, Printing colours: Cyan, Magenta, Matte black, Red, Yellow, Quantity per pack: 5 pc(s), Black ink page yield: 1640 pages

Features		Operational conditions	
Print technology	Inkjet printing	Operating relative humidity (H-H)	5 - 95%
Compatibility *	Canon PIXMA PRO-10	Storage temperature (T-T)	10 - 35 °C
Quantity per pack *	5 pc(s)	Operating temperature (T-T)	15 - 35 °C
Black ink page yield *	1640 pages	Storage relative humidity (H-H)	5 - 95%
Colour ink page yield *	710 pages	Packaging data	
Type *	Original	Package type	Blister
Cartridge capacity	Standard Yield	Other features	
Ink type	Pigment-based ink	Page yield footnote	ISO/IEC 24734
Printing colours *	Cyan, Magenta, Matte black, Red, Yellow	Logistics data	
Supply type *	Multi pack	Harmonized System (HS) code	84439990
Country of origin	Japan		
Colour	✓		



4960999974200

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.