



BenQ WDRT8192 WLAN 300 Mbit/s

Brand : BenQ

Product code: 5J.J3F28.E01

Product name : WDRT8192



WDRT8192 - USB 2.0, IEEE 802.11 b/g/n, 2.4GHz

BenQ WDRT8192 WLAN 300 Mbit/s:

The BenQ Wireless Display Adapter

The portable BenQ Wireless Display Adapter is designed to perfect every presentation experience with USB 2.0 seamless wireless WLAN connectivity. The set-up is simple. Quicker and much easier-keeping your presentation lookin' great to your audience.

BenQ WDRT8192. Connectivity technology: Wired, Host interface: USB, Interface: WLAN. Maximum data transfer rate: 300 Mbit/s, Wi-Fi band: Single-band (2.4 GHz). Product colour: Black

Ports & interfaces		System requirements	
Connectivity technology *	Wired	Windows operating systems supported	Windows 2000, Windows 2000 Professional, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
Host interface *	USB		
Interface *	WLAN		
Network			
Maximum data transfer rate *	300 Mbit/s		
Networking standards *	IEEE 802.11b, IEEE 802.11g, IEEE 802.11n		
Wi-Fi	✓		
Wi-Fi band	Single-band (2.4 GHz)		
WLAN data transfer rates supported	1,2,6,11,12,18,24,48,54,270,300 Mbit/s		
Security algorithms	128-bit WEP, 64-bit WEP, TKIP, WPA, WPA2		
Design		Minimum processor	200 MHz
Component for *	PC		
Product colour	Black	Operational conditions	
Internal *	✗	Operating temperature (T-T)	0 - 50 °C
Antenna	✗	Operating relative humidity (H-H)	5 - 90%
LED indicators	Power	Weight & dimensions	
System requirements		Width	24.4 mm
Minimum RAM	64 MB	Depth	9.9 mm
		Height	52.3 mm
		Weight	10 g
		Packaging data	
		Quantity per pack	1 pc(s)
		Package width	90 mm
		Package depth	15 mm
		Package height	10 mm
		Package weight	33.5 g
		Logistics data	
		Harmonized System (HS) code	85176990
		Other features	
		Quick start guide	✓



0840046026936



840046026936



5054629371954



4718755039980

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.