

Epson Premium Semi-Gloss Photo Paper - 10x15cm - 50 Sheets

Brand : Epson

Product code: C13S041765

Product name : Premium Semi-Gloss Photo Paper - 10x15cm - 50 Sheets

Premium Semi-Gloss Photo Paper - 10x15cm - 50 Sheets

Epson Premium Semi-Gloss Photo Paper - 10x15cm - 50 Sheets:

Premium Semigloss Photo Paper (250) delivers highly saturated prints by offering maximum ink coverage and a high D-Max for true photographic reproductions. Its 265 micron resin coated base gives prints a photographic feel, and keeps the paper cockle-free. Ideal for use with all Epson Inks. Like all Epson innovative media, this paper is engineered to give you the highest resolution and colour saturation possible. As always, Epson supplies guarantees Epson quality. Overview- Highest colour gamut available for vivid colour reproduction- Resin coated paper base for actual photo prints- Semigloss finish- Enhanced 2880 dpi printing for the highest quality output- Dries instantly for easy handling (using Epson inks)- Compatible with UltraChrome™ ink- 265 micron thickness for a durable photographic feel



Features	
Product colour	White
Finish type *	Semi-gloss
Media weight *	251 g/m²
Sheets per pack	50 sheets

Features	
Compatible products	Expression Premium XP-900
	Expression Premium XP-830
	Expression Premium XP-820
	Expression Premium XP-810
	Expression Premium XP-720
	Expression Premium XP-710
	Expression Premium XP-645
	Expression Premium XP-640
	Expression Premium XP-635
	Expression Premium XP-630
	Expression Premium XP-625
	Expression Premium XP-620
	Expression Premium XP-615
	Expression Premium XP-610
	Expression Premium XP-6005
	Expression Premium XP-6000
	Expression Premium XP-540
	Expression Premium XP-530
	Expression Premium XP-520
	Expression Premium XP-510
	Expression Photo XP-960 Expression
	Photo XP-950 Expression Photo
	XP-860 Expression Photo XP-850
	Expression Photo XP-760 Expression
	Photo XP-750 Expression Photo
	XP-55 Expression Photo HD
	XP-15000 Expression Home XP-445
	Expression Home XP-442
	Expression Home XP-435
	Expression Home XP-432
	Expression Home XP-425
	Expression Home XP-422
	Expression Home XP-415
	Expression Home XP-412
	Expression Home XP-345
	Expression Home XP-342
	Expression Home XP-335
	Expression Home XP-332
	Expression Home XP-325
	Expression Home XP-322
	Expression Home XP-315
	Expression Home XP-312
	Expression Home XP-247
	Expression Home XP-245
	Expression Home XP-235
	Expression Home XP-225
	Expression Home XP-215
	Expression Home XP-212 Epson
	Stylus Photo 2100 Epson Stylus
	Photo 1500W Epson Stylus Photo
	1400 Epson Expression Premium
	XP-800 Epson Expression Premium
	XP-700 Epson Expression Premium
	XP-605 Epson Expression Premium
	XP-600 Epson Expression Home
	XP-405WH Epson Expression Home
	XP-405 Epson Expression Home
	XP-305 Epson Expression Home
	XP-30 Epson Expression Home
	XP-205 Epson Expression Home
	XP-202 Epson Expression Home
	XP-102 EcoTank ET-7750 EcoTank
	ET-7700 EcoTank ET-4750 EcoTank
	ET-3750 EcoTank ET-3700 EcoTank
	ET-2756 EcoTank ET-2751 EcoTank
	ET-2750 EcoTank ET-2700
Weight & dimensions	
Width	150 mm
Height	100 mm
Packaging data	
Quantity per pack	1 pc(s)
Package width	105 mm
Package depth	150 mm
Package height	35 mm
Package weight	240 g

Logistics data	
Harmonized System (HS) code	37032000
Pallet length (UK)	150 cm
Pallet gross width	120 cm
Pallet gross height	100 cm
Products per pallet	20 pc(s)
Products per pallet (UK)	3040 pc(s)
Products per master (outer) case	10 pc(s)
Minimum order quantity	20 pc(s)
Other features	
Country of origin	Japan



1034383546700



0010343605169



010343605169

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.