
3M Privacy Filter for 19in Monitor, 16:10, PF190W1B

Brand : 3M

Product code: 7000013839

Product name : Privacy Filter for 19in Monitor, 16:10, PF190W1B



- Effective "black out" privacy from side views outside the 60-degree viewing angle
- Durable privacy filter that can withstand hundreds of cleanings
- Helps reduce blue light, without distorting the natural color of your display.
- A reversible solution, 3M™ Privacy Filters offer a glossy option and a matte option that help reduce glare and fingerprints.
- 100% hand inspected for quality assurance.

Privacy Filter for 19in Monitor, 16:10, PF190W1B

3M Privacy Filter for 19in Monitor, 16:10, PF190W1B:

Achieve world-class privacy with 3M™ Privacy Filters, the leading name in screen solutions. Offers exceptional clarity and security while protecting screens from hazards without affecting performance. Make 3M your first line of defense against visual hackers, damage, glare, and more—at home, in the office, and everywhere you work.

Design	
Maximum screen size *	48.3 cm (19")
Suitable for *	Monitor
Type *	Frameless display privacy filter
Screen size HxW	408 x 255 mm
Display diagonal (metric)	48.2 cm
Filter colour	Black
Reversibility	Matte-to-Glossy
Product colour	Black

Features	
Display filter features *	Anti-glare
Display types supported *	LCD
Aspect ratio	16:10
Widescreen	✔
Scratch-resistant	✔
Limits viewing angle	60°
Easy to clean	✔
Surface finish	Glossy / Matt
Screen format	Widescreen
Country of origin	United States
Easy to apply	✔
Durable screen protection	✔
Privacy filtering orientation	Landscape
Touchscreen compatible	✘
Installation type	Adhesive strip + Slide mount tab
Easy to remove	✔
Fingerprint resistant	✔
Blue light filter	✔

Weight & dimensions	
Width	408 mm
Height	255 mm
Weight	66 g

Packaging data	
Package width	457 mm
Package depth	5 mm
Package height	318 mm
Package weight	271 g

Other features	
Anti-reflective	✔
Special features	Compatible For Device With Raized Bezel
Compliance certificates	Trade Agreements Act (TAA)

Logistics data	
Pallet net height	121.9 cm
Pallet net length	121.9 cm
Pallet net width	106.7 cm
Pallet net weight	53.1 kg
Pallet weight (EU)	295.3 kg
Products per pallet (EU)	805 pc(s)
Harmonized System (HS) code	85299097
Pallet gross width	106.7 cm
Pallet gross length	121.9 cm
Pallet gross height	121.9 cm
Pallet gross weight	295.3 kg
Shipping (inner) case width	32.9 cm
Shipping (inner) case length	46.8 cm
Shipping (inner) case height	4.8 cm
Shipping (inner) case gross weight	1.73 kg
Shipping (inner) case net weight	330 g
Products per shipping (inner) case	5 pc(s)

Features		Logistics data	
Compatibility	LG Flatron 19MB35DE; Samsung SyncMaster 920NW; ViewSonic VX1945wm-3; Dell P1909W; LG Flatron 19MB35PM-W; ViewSonic VA916a-LED; Dell 1909Wb; Dell E1910; Dell UltraSharp 1908WFP; Lenovo ThinkVision L1951; Dell E198WFP; Samsung S19C200BW; Samsung S19C450BW; Lenovo ThinkCentre A70z 1165; Samsung S19B420BW; LG E1910HW; Samsung SyncMaster B1940EW; Dell S199WFP; Samsung S19C330HW; Samsung S19C350NW	Shipping (inner) case GTIN (EAN/UPC)	50051128786142



0912000153863




912000153863




0767872165472



767872165472



5054533629226



5055410402437



0172302721478



172302721478



0163120799664



163120799664



0809392590560



809392590560



0809190606838




809190606838




0638084744956




638084744956



7426801324399




5052461814523



5596692301686



5052883396065




5147841649120



0809185301878




809185301878




5197264776637


Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date



0809385151433




809385151433



0887621168735



887621168735



5054184109849



5054242066275



0801593276595



801593276595



0809391334844



809391334844



0820294269507



820294269507




0132018264676



132018264676




0804993539598



804993539598




5053252759221




0820114572251



820114572251



5711783907626



5054484629221





0051128786147



051128786147

5715063640586

5715063701256

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date