

Brother LC125XLRBWP ink cartridge 3 pc(s) Original High (XL) Yield Cyan, Magenta, Yellow

Brand : Brother

Product code: LC125XLRBWP

Product name : LC125XLRBWP

Ink Cartridge Pack: Cyan / Magenta / Yellow



Brother LC125XLRBWP ink cartridge 3 pc(s) Original High (XL) Yield Cyan, Magenta, Yellow:

This cartridge works with DCP-J4110DW / MFC-J4410DW / MFC-J4510DW / MFC-J4710DW / MFC-J6520DW / MFC-J6720DW / MFC-J6920DW and yields up to 1,200 pages. Brother ink cartridges are designed to work perfectly with our printers, giving you excellent results and value for money. Brother consider the environmental impact at every stage of your ink cartridge life cycle, reducing waste at landfill. All our hardware and ink cartridges are built to have as little impact on the environment as possible. Genuine Brother LC125XLRBWP high ink cartridges - worth it every time
Brother LC125XLRBWP. Colour ink type: Pigment-based ink, Cartridge capacity: High (XL) Yield, Supply type: Multi pack, Colour ink page yield: 1200 pages, Printing colours: Cyan, Magenta, Yellow, Quantity per pack: 3 pc(s)

Features		Weight & dimensions	
Colour ink type	Pigment-based ink	Depth	122 mm
Print technology	Inkjet printing	Height	177 mm
Compatibility *	- MFC-J4510DW	Weight	150 g
Quantity per pack *	3 pc(s)	Packaging data	
Colour ink cartridges quantity	3	Package weight	210 g
Colour ink page yield *	1200 pages	Package type	Blister
Type *	Original	Logistics data	
Cartridge capacity	High (XL) Yield	Pallet gross height	16.2 cm
Ink type	Pigment-based ink	Products per pallet	992 pc(s)
Printing colours *	Cyan, Magenta, Yellow	Master (outer) cases per pallet	248 pc(s)
Brand compatibility *	Brother	Layers per pallet	8 pc(s)
Supply type *	Multi pack	Master (outer) cases per pallet layer	31 pc(s)
Country of origin	China	Pallet gross weight	200 kg
Weight & dimensions		Harmonized System (HS) code	84439990
Width	86 mm	Pallet type	1200 x 1000 mm



5014047563348

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.