

## ASUS PA148CTV computer monitor 35.6 cm (14") 1920 x 1080 pixels Full HD LED Touchscreen Tabletop Black

**Brand :** ASUS

**Product code:** 90LM06E0-B02170

**Product name :** PA148CTV



- 14-inch Full HD IPS anti-glare panel with capacitive 10-point multitouch
  - ASUS Dial and Virtual Control Panel provide productivity-enhancing shortcuts and programmable hotkeys for compatible Adobe software (for example, Adobe Photoshop, Photoshop Lightroom Classic, Premiere Pro and After Effects)
  - 100% sRGB and 100% Rec. 709 color gamut, and Calman Verified with factory pre-calibrated Delta E < 2 for exceptional color accuracy
  - User-friendly design with Intuitive OSD control via ASUS Dial, metal kickstand and tripod socket
  - I/O ports include two USB Type-C® ports (DP Alt mode) and one Micro HDMI for variety devices connection
  - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- 14", IPS, Full HD, 1920 x 1080, 100% sRGB, 60Hz, 5ms, 10-point Touch, 2 x 1W speaker, 2 x USB-C, Micro HDMI, 326.1 x 204.4 x 12 mm, 0.74 kg



| Display                        |                             | Design                                    |            |
|--------------------------------|-----------------------------|-------------------------------------------|------------|
| Display diagonal *             | 35.6 cm (14")               | Product colour *                          | Black      |
| Display resolution *           | 1920 x 1080 pixels          | <b>Ports &amp; interfaces</b>             |            |
| HD type *                      | Full HD                     | Built-in USB hub *                        | ✓          |
| Native aspect ratio *          | 16:9                        | Number of upstream ports                  | 1          |
| Display technology *           | LED                         | USB Type-C DisplayPort Alternate Mode     | ✓          |
| Panel type *                   | IPS                         | DVI port                                  | ✗          |
| Touchscreen *                  | ✓                           | HDMI *                                    | ✗          |
| Touchscreen type               | Tabletop                    | Micro HDMI ports quantity                 | 1          |
| Touchscreen technology         | Projected capacitive system | Headphone out *                           | ✗          |
| Touch technology               | Multi-touch                 | <b>Ergonomics</b>                         |            |
| Display brightness             | 300 cd/m²                   | Cable lock slot *                         | ✓          |
| Response time *                | 5 ms                        | Cable lock slot type                      | Kensington |
| Screen shape *                 | Flat                        | Height adjustment *                       | ✗          |
| Supported graphics resolutions | 1920 x 1080 (HD 1080)       | <b>Power</b>                              |            |
| Contrast ratio (typical) *     | 700:1                       | Energy efficiency class (SDR) *           | E          |
| Viewing angle, horizontal      | 178°                        | Energy consumption (SDR) per 1000 hours * | 9 kWh      |
| Viewing angle, vertical        | 178°                        | Energy efficiency scale                   | A to G     |
| Display number of colours *    | 16.7 million colours        | <b>Weight &amp; dimensions</b>            |            |
| Pixel pitch                    | 0.16 x 0.16 mm              | Width (with stand)                        | 326.1 mm   |
| Viewable size, horizontal      | 30.9 cm                     | Depth (with stand)                        | 12 mm      |
| Viewable size, vertical        | 17.4 cm                     | Height (with stand)                       | 204.4 mm   |
| sRGB coverage (typical)        | 100%                        | Weight (with stand)                       | 740 g      |
| <b>Performance</b>             |                             | <b>Packaging data</b>                     |            |
| NVIDIA G-SYNC *                | ✗                           | Package width                             | 413 mm     |
| AMD FreeSync *                 | ✗                           | Package depth                             | 90 mm      |
| Low Blue Light technology      | ✓                           | Package height                            | 342 mm     |
| <b>Multimedia</b>              |                             | Package weight                            | 2.5 kg     |
| Number of speakers             | 1                           |                                           |            |
| RMS rated power                | 2 W                         |                                           |            |
| Built-in speaker(s) *          | ✓                           |                                           |            |
| Built-in microphone            | ✗                           |                                           |            |

| Multimedia        |   | Packaging content |                                      |
|-------------------|---|-------------------|--------------------------------------|
| Built-in camera * | ✗ | Cables included   | Micro-HDMI, USB Type-C to USB Type-A |



4718017862233



0192876862230



192876862230

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.