



APC SRV240RLBP-9A UPS battery Sealed Lead Acid (VRLA) 240 V

Brand : APC
Product code: SRV240RLBP-9A
Product name : SRV240RLBP-9A



- Extended-run battery systems provide flexible runtime to critical Smart-UPS applications
 - Includes: Documentation CD, User Manual
- Easy UPS SRV 240V RM Battery Pack for 6&10kVA Rack, Extended Runtime model

APC SRV240RLBP-9A UPS battery Sealed Lead Acid (VRLA) 240 V:

APC Easy UPS SRV 240V RM Battery Pack for 6&10kVA Rack, Extended Runtime model
Extended-run battery systems provide flexible runtime to critical Smart-UPS applications.
Includes: Documentation CD, User Manual
APC SRV240RLBP-9A. Battery technology: Sealed Lead Acid (VRLA), Battery voltage: 240 V, Number of batteries included: 20 pc(s). Compliance certificates: RoHS, Certification: REACH. Weight: 60 kg, Width: 190 mm, Height: 368 mm. Package width: 290 mm, Package height: 570 mm, Package depth: 460 mm



Features		Packaging data	
Battery technology *	Sealed Lead Acid (VRLA)	Package height	570 mm
Battery voltage *	240 V	Package depth	460 mm
Number of batteries included *	20 pc(s)	Package weight	63 kg
Product colour	Black	Operational conditions	
Certificates		Storage temperature (T-T)	-15 - 40 °C
Compliance certificates	RoHS	Operating relative humidity (H-H)	0 - 95%
Certification	REACH	Storage relative humidity (H-H)	0 - 95%
Weight & dimensions		Operating altitude	0 - 1000 m
Weight	60 kg	Non-operating altitude	0 - 15000 m
Width	190 mm	Logistics data	
Height	368 mm	Harmonized System (HS) code	85044095
Depth	485 mm	Total carbon footprint (kg of CO2e)	320.53
Packaging data			
Package width	290 mm		



0731304343356



731304343356

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.