

StarTech.com HDMI Over IP Extender Kit with Advanced Compression

Brand : StarTech.com

Product code: ST12MHDLNHK

Product name : HDMI Over IP Extender Kit with Advanced Compression



- Efficiently distribute video throughout your site using your local area network
 - Easily create your ideal digital signage with a versatile and scalable video distribution system
 - Deliver brilliant HD quality video with 1080p support
 - Newer Version Available: ST12MHDLAN2K features longer range (100m/330ft) and video wall support
- StarTech.com HDMI Over IP Extender Kit - Advanced Compression - Transmitter & Receiver (ST12MHDLNHK)

StarTech.com HDMI Over IP Extender Kit with Advanced Compression. Type: AV transmitter & receiver, Maximum resolution: 1920 x 100 pixels, Cable types supported: Cat5e, Cat6. Connectivity technology: Wired, USB connector type: Mini-USB B, Audio input: 3.5 mm. AC input voltage: 100 - 240 V, Operating voltage: 5 V, Input current: 0.3 A. Weight: 3.2 kg. Package width: 92 mm, Package depth: 108 mm, Package height: 24 mm



Features		Power	
Type *	AV transmitter & receiver	Output current	1 A
Maximum resolution *	1920 x 100 pixels	Operational conditions	
Cable types supported	Cat5e, Cat6	Operating temperature (T-T)	0 - 40 °C
Maximum transfer distance	15 m	Storage temperature (T-T)	-10 - 60 °C
Maximum refresh rate	60 Hz	Operating relative humidity (H-H)	0 - 80%
Audio output channels	2.0 channels	Weight & dimensions	
LED indicators	Status	Weight	3.2 kg
Supported video modes	1080p	Packaging data	
Material	Aluminium	Package width	92 mm
Rack mounting	✓	Package depth	108 mm
Daisy chain	✓	Package height	24 mm
Rubber feet	✓	Packaging content	
Product colour	Black	AC adapter included	✓
Ports & interfaces		Cables included	LAN (RJ-45), Serial, USB
Connectivity technology *	Wired	Included power plug types	ANZ, EU, NA, UK
RJ-45 input ports	1	Manual	✓
RJ-45 output ports	1	IR blaster included	✓
HDMI in	1	IR receiver included	✓
Number of HDMI outputs	1	Remote control included	✓
USB ports quantity	2	Mounting brackets included	✓
USB connector type	Mini-USB B	Technical details	
Audio input	3.5 mm	Sustainability compliance	✓
Audio output	3.5 mm	Compliance certificates	CE, Federal Communications Commission (FCC), RoHS, Trade Agreements Act (TAA)
Remote (IR) input	1		
Remote (IR) output	1		
Power			
AC input voltage	100 - 240 V		
Operating voltage	5 V		

Power		Logistics data	
Input current	0.3 A	Master (outer) case width	324 mm
		Master (outer) case length	406 mm
		Master (outer) case height	262 mm
		Products per master (outer) case	6 pc(s)



0065030878760



065030878760

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.