

Epson WorkForce DS-70



Brand : Epson

Product family: WorkForce

Product code: B11B252402

Product name : WorkForce DS-70

WorkForce DS-70

[Epson WorkForce DS-70:](#)

Scan anywhere

The small, compact design and USB connectivity make it easy to use the DS-70 wherever it's needed, such as in reception areas, and stores conveniently in a drawer.

Highly organised

Software provided with the DS models includes Document Capture Pro 2 and Epson Scan 2.0, and TWAIN driver support, making it easier to scan, save and share information around the business. Advanced features for naming, separating and routing documents make scanning easy – and logical. Users can save and send files in common formats like PDF, JPEG, TIFF and many more. Continuous scanning with automatic feed mode speeds up the scanning process, while the CIS sensor delivers instant scanning with no warm up time.

Flexible

The ability to scan a wide range of document and media types makes this model a reliable asset. It handles paper from 35gsm to 270gsm, and long paper up to 1.8 metres.

Scanning		Packaging data	
Maximum scan size *	216 x 356 mm	Package weight	553 g
Optical scanning resolution *	600 x 600 DPI	Packaging content	
Colour scanning	✓	Cables included	USB
Duplex scanning *	✗	Bundled software	Document Capture Pro 2.0, Epson Scan 2
Input colour depth	48 bit	System requirements	
Output colour depth	24 bit	Compatible operating systems	Mac OS 10.6+, Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Server 2003, Windows Server 2008 (32/64 Bit), Windows Server 2012 R2, Windows Server 2016, Windows Vista, Windows XP
Input greyscale depth	16 bit		Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP
Output greyscale depth	8 bit	Windows operating systems supported	Mac OS X 10.10 Yosemite, Mac OS X 10.11 El Capitan, Mac OS X 10.12 Sierra, Mac OS X 10.13 High Sierra, Mac OS X 10.14 Mojave, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Output monochrome depth	8 bit	Mac operating systems supported	Windows Server 2003, Windows Server 2008, Windows Server 2008 x64, Windows Server 2012 R2, Windows Server 2016
Scan speed (b/w, low res, A4)	5.5 sec/page		
Scan speed (colour, low res, A4)	5.5 sec/page	Operational conditions	
Design		Operating temperature (T-T)	5 - 35 °C
Scanner type *	Handheld scanner	Storage temperature (T-T)	-25 - 60 °C
Product colour *	White	Operating relative humidity (H-H)	10 - 85%
Built-in display *	✗	Storage relative humidity (H-H)	10 - 90%
Performance		Other features	
Sensor type *	CIS	Output resolutions	600 dpi
Light source	ReadyScan LED	Image formats supported	BMP, JPEG, TIFF, PNG
Scan file formats	BMP, JPEG, PDF, PNG, TIFF		
Daily duty cycle (max) *	300 pages		
Scan drivers	TWAIN, WIA, SANE, ICA		
Input capacity			
Auto document feeder (ADF) input capacity	1 sheets		
Paper handling			
Scanning media types supported	Business Card, Plastic Card, Post Card(JPN)		
Maximum ISO A-series paper size *	A4		
Paper tray media weight	35 - 270 g/m²		
Auto Document Feeder (ADF) media weight	35 - 270 g/m²		

Ports & interfaces		Logistics data	
USB port *	✓	Products per pallet	360 pc(s)
USB version	2.0	Country of origin	China
Standard interfaces	USB 2.0	Pallet gross weight	0 g
Power		Master (outer) case length	360 mm
Power supply type *	USB	Master (outer) case height	320 mm
Weight & dimensions		Master (outer) case width	350 mm
Width	272 mm	Master (outer) case gross weight	0 g
Depth	47 mm	Pallet gross length	120 cm
Height	34 mm	Pallet gross width	80 cm
Weight	270 g	Pallet gross height	171 cm
Packaging data		Products per master (outer) case	10 pc(s)
Quantity per pack	1 pc(s)	Products per pallet layer	60 pc(s)
Package width	140 mm	Products per pallet layer (UK)	60 pc(s)
Package depth	330 mm	Products per pallet (UK)	360 pc(s)
Package height	65 mm	Pallet weight (UK)	0 g
		Pallet length (UK)	120 cm
		Pallet width (UK)	100 cm
		Pallet height (UK)	171 cm
		Master (outer) case GTIN (EAN/UPC)	8715946662596
		Harmonized System (HS) code	84716070



8715946662831

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.